



E Series Keystone Modular Jack, 8-position, category 6, unshielded UTP, RJ45, violet

OBSOLETE

This product was discontinued on: June 30, 2019

Replaced By:

1-2291216-0
KJ610 JACK-VIO

KJ Series Keystone Modular Jack, 8-position, category 6, violet

760237660
UKJ600-VIO

Uniprise UKJ Series Keystone Modular Jack, RJ45, category 6, T568A/T568B, unshielded, without dust cover, violet

Product Classification

Regional Availability

Asia | Latin America | North America

Portfolio

NETCONNECT®

Product Type

Modular jack

Product Series

E Series

General Specifications

ANSI/TIA Category

6

Cable Type

Unshielded

Color

Violet

Conductor Type

Solid | Stranded

Integrated Dust Cover Type

None

Mounting

KL Series faceplates and panels

Outlet Type

Keystone

Termination Punchdowns, minimum

100 times

Termination Tool

SL Termination tool

Termination Type

IDC

1-2111475-0

Transmission Standards ANSI/TIA-568-C.2 | ISO/IEC 11801 Class E

Wiring T568A | T568B

Dimensions

Panel Cutout, recommended 14.78 x 20.07 mm (0.58 x 0.79 in)

Panel Thickness, recommended 1.6 mm | 0.063 in

Height 16.13 mm | 0.635 in

Width 14.48 mm | 0.57 in

Depth 30.48 mm | 1.2 in

Compatible Cable Diameter, maximum 5.8 mm | 0.228 in

Compatible Insulated Conductor Diameter, maximum 1.27 mm | 0.05 in

Contact Plating Thickness 1.27 μ m

Compatible Conductor Gauge, solid 24–22 AWG

Compatible Conductor Gauge, stranded 26–24 AWG

Electrical Specifications

Contact Resistance, maximum 1 mOhm

Current Rating, maximum 0.75 A

Insulation Resistance, minimum 10 MOhm

Safety Voltage Rating 150 Vac

Material Specifications

Contact Base Material Beryllium copper

Contact Plating Material Gold

Material Type Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Flammability Rating UL 94 V-0

Safety Standard UL 1863 | cUL

1-2111475-0

Packaging and Weights

Packaging Type

Bag

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

