

## PowerSUM MPS100E Category 5e U/UTP Information Outlet, cream



- Modified outlet termination scheme to match other Systimax outlets and to align with the MGS400 and the MGS600 outlets

### OBSOLETE

This product was discontinued on: January 15, 2023

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Modular jack
<b>Product Brand</b>	PowerSUM
<b>Product Series</b>	MPS100E

## General Specifications

<b>ANSI/TIA Category</b>	5e
<b>Cable Type</b>	Unshielded
<b>Color</b>	Cream
<b>Conductor Type</b>	Solid   Stranded
<b>Integrated Dust Cover Type</b>	None
<b>Mounting Note</b>	Color matches with M-series Cream Faceplates
<b>Termination Type</b>	IDC
<b>Wiring</b>	T568A   T568B

## Dimensions

<b>Height</b>	20.32 mm   0.8 in
<b>Width</b>	20.32 mm   0.8 in
<b>Depth</b>	30.48 mm   1.2 in

# 108480484 | MPS100E-215

---

**Compatible Conductor Gauge, solid** 22 AWG | 24 AWG

**Compatible Conductor Gauge, stranded** 22 AWG | 24 AWG

## Electrical Specifications

**Contact Resistance Variation, maximum** 20 mOhm

**Contact Resistance, maximum** 100 mOhm

**Current Rating at Temperature** 1.5 A @ 20 °C | 1.5 A @ 68 °F

**Dielectric Withstand Voltage, RMS, conductive surface** 1,500 Vac @ 60 Hz

**Dielectric Withstand Voltage, RMS, contact-to-contact** 1,000 Vac @ 60 Hz

**Insulation Resistance, minimum** 500 MOhm

**Remote Powering** Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002

## Material Specifications

**Contact Plating Material** Precious metals

**Material Type** Copper alloy | High-impact, flame retardant, thermoplastic

**Termination Contact Plating** Nickel

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

**Plug Insertion Life, test plug** IEC 60603-7 compliant plug

**Plug Retention Force, minimum** 133 N | 29.9 lbf

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

**Flammability Rating** UL 94 V-0

**Safety Standard** UL | cUL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

