


1375191-3



SL110 Series Modular Jack, 8-position, RJ45, category 5e, T568A /T568B, unshielded, without dust cover, white

OBSOLETE

This product was discontinued on: June 13, 2018

Replaced By:

1-1375191-3
SL110-5E-P.WH

SL-Series Modular Jack, RJ45, Cat5e Unshielded, ProWhite

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

NETCONNECT®

Product Type

Modular jack

Product Series

SL Series

General Specifications

ANSI/TIA Category

5e

Cable Type

Unshielded

Color

White

Conductor Type

Solid | Stranded

Integrated Dust Cover Type

None

Mounting

SL Series faceplates and panels

Outlet Type

Standard

Termination Punchdowns, minimum

200 times

Termination Tool

SL Termination tool

Termination Type

IDC

Transmission Standards

ANSI/TIA-568-C.2 | ISO/IEC 11801 Class D

1375191-3

Wiring T568A | T568B

Dimensions

Panel Cutout, recommended 14.78 x 20.07 mm (0.58 x 0.79 in)

Panel Thickness, recommended 1.6 mm | 0.063 in

Height 16.26 mm | 0.64 in

Width 14.48 mm | 0.57 in

Depth 30.48 mm | 1.2 in

Compatible Insulated Conductor Diameter, maximum 1.45 mm | 0.057 in

Contact Plating Thickness 1.27 µm

Compatible Conductor Gauge, solid 24–22 AWG

Compatible Conductor Gauge, stranded 26–24 AWG

Electrical Specifications

PoE Durability Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles

Safety Voltage Rating 150 Vac

Material Specifications

Contact Base Material Beryllium copper

Contact Plating Material Gold

Material Type Polycarbonate

Mechanical Specifications

Plug Retention Force, minimum 89 N | 20.008 lbf

Plug to Jack Mating Cycles Complies to IEC 60603-7 series

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Flammability Rating UL 94 V-0

Safety Standard CSA | cUL

Packaging and Weights

Included Strain relief cap

Packaging quantity 1

Packaging Type

Bag

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

