
760249728 | 0-048-LN-8Z-M12BK/22G/093



Fiber OSP cable, PE, Loose Tube Gel-filled, 48 fiber, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand

Portfolio CommScope®
Product Type Fiber OSP cable

Product Series O-LN

General Specifications

 Cable Type
 Stranded loose tube

Construction TypeNon-armoredSubunit TypeGel-filled

Filler, quantity 2

Jacket Color Black

Jacket Marking Meters

Subunit, quantity 4
Fibers per Subunit, quantity 12

Total Fiber Count 48


Dimensions

Buffer Tube/Subunit Diameter2.2 mm0.087 inDiameter Over Jacket10.5 mm0.413 in

Representative Image



760249728 | 0-048-LN-8Z-M12BK/22G/093



Material Specifications

Jacket Material High density polyethylene (HDPE)

Mechanical Specifications

Minimum Bend Radius, loaded210 mm8.268 inMinimum Bend Radius, unloaded105 mm4.134 in

Tensile Load, long term, maximum 890 N | 200.08 lbf

Tensile Load, short term, maximum 2700 N | 606.984 lbf

Compression 20 N/mm | 114.203 lb/in

Compression Test Method IEC 60794-1-2 E3

Flex 25 cycles

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-21 E1

Optical Specifications

Fiber Type G.652.D and G.657.A1 | OS2

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.22 dB/km @ 1,550 nm | 0.38 dB/km @ 1,310 nm

Environmental Specifications

Installation temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Page 2 of 3



760249728 | 0-048-LN-8Z-M12BK/22G/093

Environmental Space Buried | Ducted | Outdoor

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5B

Environmental Test Specifications

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method IEC 60794-1-2 F1

Packaging and Weights

Cable weight 86 kg/km | 57.789 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

