

## C4® CMTS Release 8.2.5



## **PRODUCT OVERVIEW:**

The ARRIS C4® CMTS is a high-availability, highly dense DOCSIS® 3.0 system designed to deliver the stability and throughput that MSOs require for advanced services. It features a 21 slot chassis with a midplane-based architecture designed for continuous system operation. This unique architecture allows the C4 CMTS to provide carrier-grade integrated Layer 3 edge routing, hitless RF sparing, and advanced CMTS functionality in a single chassis. The following modules are supported:

- System Control Module (SCM), including support for the SCM II, SCM II EM, SCM II EM(U), and SCM 3
- Router Control Module (RCM)
- Downstream and Upstream Cable Access Modules (CAMs) 16D CAM, XD CAM, 12U CAM, 24U CAM





Release 8.2.5 delivers a significant set of value-added capabilities for E6000® CER customers. With Rel. 8.2.5, cable operators deploying the C4 CMTS can utilize a 5 – 85 MHz band for the return frequency spectrum (24U CAM only) and also are able to bond up to eight (8) upstream channels (24U CAM only). Mulit-Protocol BGP routing support with the IPv6 Address Family is included in Rel. 8.2.5; this provides an important Layer 3 capability for operators deploying IPv6. Rel. 8.2.5 also supports marking the DiffServ Code Point (DSCP) for downstream subscriber traffic which allows MSOs to apply QoS principles within the subscriber premises. In addition, Rel. 8.2.5 supports a PCMM ECN which allows a single gate to use both an IPv4 and an IPv6 classifier; Rel. 8.2.5 also supports Password Challenge functionality for RADIUS Authentication.

## **FEATURES**

- DSCP Marking for DHCP Packets
- PCMM ECN MM-N-13.0697-1 Support (IP4 and IPv6 Classifiers per Gate)
- DSCP Marking for Downstream Subscriber Traffic
- RADIUS Password Challenge
- Bonding of 8 US (24U CAM)
- Support for Multi-tuner Modems (without static RCCs)

- CLI Assignment for BSoD L2VPNs
- Annex A Mixed Modulation per F Connector
- 5 85 MHz Support (24U CAM)
- MP-BGP w/ IPv6 Address Family
- Intelligent TCS Assignment
- TCS Reduction
- MIB Support for Modem Count per Fiber Node

Copyright Statement: @ARRIS Enterprises, Inc. 2015 All rights reserved. No part of this publication may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from ARRIS Enterprises, Inc. ("ARRIS"). ARRIS reserves the right to revise this publication and to make changes in content from time to time without obligation on the part of ARRIS to provide notification of such revision or change. ARRIS and the ARRIS logo are all trademarks of ARRIS Enterprises, Inc. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks and the names of their products. ARRIS disclaims proprietary interest in the marks and names of others.

**Note:** The capabilities, system requirements and/or compatibility with third-party products described herein are subject to change without notice.





Managing the C4 CMTS is typically done via the SNMP or CLI interfaces. The C4 CMTS has multiple options available for IPDR, a useful tool for measuring bandwidth usage. Physical maintenance of the C4 CMTS is very simple. Air filters should be inspected and/or replaced per recommendations in the C4 CMTS User Guides.

GENERAL SPECIFICATI	ONS
RF Downstream	
Frequency Range (MHz)	91 to 999 (DOCSIS® 3.0); 112 to 999 (EuroDOCSIS™ 3.0)
Modulation (QAM)	64, 256
Data Rate (Mbps) (Max.)	30.34 to 55.62 per channel
RF Output Level (dBmV)	41 to 60
Symbol Rate (Msym/sec)	5.361 (DOCSIS); 6.952 (EuroDOCSIS)
Bandwidth (MHz)	6 (DOCSIS), 8 (EuroDOCSIS)
Output (load) impedance (ohms)	75
Physical	
Power	-48 VDC (-44 to -72 VDC)
Power Consumption (full-fill system)	2,800 W max at -48 VDC, 77°F (25°C)
Operating Temperature:	
Short Term °F (°C)	+23 to +131 (-5 to +55)
Long Term °F (°C)	+41 to +104 (+5 to +40)
Storage Temperature °F (°C	C) -40 to +158 (-40 to +70)
Operating Humidity (Min Max.)	5 to 85% (Non condensing)
Dimensions (H x W x D) in. (cm)	24.5 x 17.4 x 20.0 (62.2 x 44.2 x 50.8)
Weight lbs. (kg) (full-fill system)	178 (80.9)

RF Upstream			
Frequency Range (MHz)		5 to 85 MHz (24U CAM) 5 to 65 MHz (12U CAM)	
Modulation		QPSK, 16 QAM, 32 QAM, 64 QAM	
Channel Type		TDMA, ATDMA, TDMA/ATDMA	
Data Rate (Mbps) (Max.)		30.72 per channel	
RF Input Level (dBmV)		-16 to +29	
Frequency Resolution (KHz)		<1	
Installation Environ	ment		
Management Interfaces		10/100/1000 Mbps Ethernet (RJ-45) plus Console (serial port, RJ45)	
Network-side Interfaces	10 G	igabit Ethernet (SFP+) auto-baud, eight per card	
Connector Access		Ethernet ports via front of chassis, management s via rear	
Management Acces	s		
In-band Manageme	nt with	Access Control Lists via any NSI port	
Out-of-Band Manag	ement	via dedicated Ethernet port on SCM	
Console (serial) port	on SC	M PIC	





The C4 CMTS provides cable operators with significant improvements in DC power consumption per downstream channel as compared to other DOCSIS 3.0 platforms. This leads to reduced powering and cooling requirements for the operators' facilities, which can provide savings in operational and capital expenditures.

782181

782182

713877

ORDERING INFORMATION

Speed Fans

SOFTWARE RELEASE 8.2.5 FEATURES (PARTIAL LISTING)			
DSCP Marking for DHCP Packets	IPv6 Support, Including:		
PCMM ECN Support (IP4 and IPv6 Classifiers per Gate)	IS-IS Multi-Topology Support		
DSCP Marking for Downstream Subscriber Traffic	OSPFv3		
RADIUS Password Challenge	DHCPv6 Prefix Delegation with Route Injection		
Bonding of 8 US (24U CAM)	Cable Source Verify with DHCP Lease Query		
Support for Multi-tuner Modems (without static RCCs)	TFTP Enforce & Dynamic Shared Secret for IPv6 CMs		
CLI Assignment for BSoD L2VPNs	DOCSIS 3.0 Multicast IP Video Support (via IGMPv3)		
Annex A Mixed Modulation per F Connector	Multicast CAC for IP Video (Phase 1)		
5 – 85 MHz Support (24U CAM)	Policy-Based Routing with Recursive Next Hop		
MP-BGP w/ IPv6 Address Family	Dynamic CM Load Balancing, including Cross-MAC Domain		
Intelligent TCS Assignment	16D CAM, XD CAM		
TCS Reduction	12U CAM, 24U CAM		
MIB Support for Modem Count per Fiber Node	BSoD L2 VPN		
Ethernet Link Aggregation (1 Gbps ports)	BPI+ Enforce		
Integrated Service Class Agility	TFTP Enforce and Dynamic Shared Secret		
IPv6 Support for PCMM	Integrated Upstream Agility		
Load Balancing of D3.0 Voice Flows (DS and US)	PIM-SSM, IGMPv2, and static multicast		
DSG 3.0	RIPv2 (RFC 1723), OSPFv2 (RFC 2328), IS-IS, BGPv4		
Extended CM Transmit Power (for USCB)	SII Lawful Intercept (RFC 3924)		
002 10 \ /   A N   +===i==			

	speed rans
799087	System Control Module (SCM) 3 (requires Rel. 8.2 or later software)
793931	System Control Module II Enhanced Memory (Updated) (SCM II EM(U))
722013	Router Control Module (RCM)
722891	Router Control Module Crossover Connector
794041	Optimized 24D Cable Access Module (CAM) Kit (Active) Licensed for 24 Downstreams, EuroDOCSIS 3.0
794044	Optimized 24D Cable Access Module (CAM) Kit (Spare) Licensed for 24 Downstreams, EuroDOCSIS 3.0
794042	Optimized 32D Cable Access Module (CAM) Kit (Active) Licensed for 32 Downstreams, DOCSIS 3.0
794045	Optimized 32D Cable Access Module (CAM) Kit (Spare) Licensed for 32 Downstreams, DOCSIS 3.0
790562	24U Cable Access Module (CAM) Kit (Even) Licensed for 24 Upstreams, DOCSIS/EuroDOCSIS 3.0
790563	24U Cable Access Module (CAM) Kit (Odd) Licensed for 24 Upstreams, DOCSIS/EuroDOCSIS 3.0
790564	24U Cable Access Module (CAM) Kit (Spare) Licensed for 24 Upstreams, DOCSIS/EuroDOCSIS 3.0
708387	Software Maintenance - Phone Plus Gold (Required)
Full price	e list available from ARRIS.

C4 CMTS System Software Release 8.2 DOCSIS 3.0 Licensed per Downstream for 16D/XD CAM

C4 CMTS System Software Release 8.2 DOCSIS 3.0 Licensed per Upstream for 12U/24U CAM

C4 Chassis, 21 Slot Chassis Assembly 14RU Chassis, 3 High

802.1Q VLAN tagging

Copyright Statement: @ARRIS Enterprises, Inc. 2015 All rights reserved. No part of this publication may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from ARRIS Enterprises, Inc. ("ARRIS"). ARRIS reserves the right to revise this publication and to make changes in content from time to time without obligation on the part of ARRIS to provide notification of such revision or change. ARRIS and the ARRIS logo are all trademarks of ARRIS Enterprises, Inc. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks and the names of their products. ARRIS disclaims proprietary interest in the marks and names of others.