



WRSS wraparound repair heat shrink sleeve kit, cables with 0.60 to 3.00 inches cable diameter, 48 inches long

- Accommodates a wide range of pressure and temperature, ideal for hostile environments
- Designed to be used for diameter transitions in cable where a large shrink ratio is required
- Minimized total required splice length allowing installation on existing cables in confined areas

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	North America
Product Type	Heat shrink repair sleeve
Product Series	WRSS

General Specifications

Color	Black
Sealant Type	Hotmelt adhesive

Dimensions

Length	1,219.2 mm 48 in
Expanded Inside Diameter, minimum	300 mm 11.811 in
Recovered Inside Diameter, maximum	60 mm 2.362 in
Single Cable Diameter, maximum	76.2 mm 3 in
Single Cable Diameter, minimum	15.24 mm 0.6 in

Material Specifications

Material Type	SuperSleeve sealing
----------------------	---------------------

Environmental Specifications

Environmental Space	Aerial Buried
----------------------------	-----------------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

