

FEATURES

- Optimize headend and hub efficiencies with industry leading density and low power consumption up to 20 transmitters or 40 receivers per 2RU chassis
- Up to 44 full spectrum wavelengths for harvesting new bandwidth through node segmentation
- Support multiple optical architectures including full spectrum, overlay, and RFoG
- Integrated optical passives for further reduction of footprint
- DOCSIS® 3.1 support for future capacity expansion to 1.2 GHz downstream, 300 MHz upstream
- Transmitters with variable output reduce need for troublesome optical attenuators
- Front or rear fiber connection simplifies installation and cable management
- Configure, monitor, and manage with CORView™ Element Management System

CommScope products and solutions can help cable operators attain new subscriber revenue and higher average revenue per subscriber without major CAPEX. Cable operators can seamlessly and easily stay in line with future goals, add new services, and strongly position against the competition.

As part of the CHP Max Headend Optics Platform, CHP Max5000® headend chassis applications unite HFC and digital transport onto a single scalable system, allowing service providers to accelerate deployment of VOD, high speed data, telephony, and other advanced services in a space-saving footprint.



Flexible Options

The CHP Max5000 offers 13 module slots in a 2RU chassis, providing 10 module slots for application modules, 2 for isolated redundant power supplies, and 1 for a local or remote management module. The high-speed backplane supports data communication in gigabit EPON applications, while a high-speed shelf interconnect option with a 100 BaseT Ethernet connection provides daisy chaining capability for multiple chassis. Front or rear fiber connection options provide flexibility in installation and maintenance.

CHP Max5000 Chassis

The CHP Max5000 (2RU) chassis fits into a 19-inch or 23-inch rack that holds 10 single-width application modules, and routes power and element management signals. An optional bracket kit is available for installation into a 23-inch rack. Each chassis requires one power supply module and accepts a second for redundancy. A high-speed shelf interconnect option with a 100 BaseT Ethernet connection provides daisy chaining capability for multiple chassis.

Modules slide into the chassis from the front of the rack, with either front or rear optical connections. Separate interfaces built into the back panel of each chassis provide power and data communications to and from installed application modules. Universal slots accept the plug-in application modules in virtually any combination to accommodate a variety of service delivery requirements. The chassis provides universal management through the Craft interface, SNMP with HMS, or remote IP access via a Craft Management Module (CMM) or System Management Module (SMM).

Designed for thermal efficiency, the CHP Max5000 chassis provides a wide operational temperature range for maximum reliability. A plenum with eight cooling fans offers better reliability than module-based fans; in the event of a fan failure, application modules—and the services provided—remain in operation.

CHP Max5000 Power Supply*

CHP Max5000 isolated, load-sharing, redundant power supplies are efficient, switched-mode modules that accept either AC or DC input. One power supply supports a completely loaded chassis, while two offer power redundancy that eliminates service interruption if one power supply or line-in feed service fails.

The CHP Max5000 switched-mode AC power supplies accepts AC input from 85 to 264 VAC (47 to 63 Hz) and provides DC voltages to drive application modules. Each chassis accepts a second backup AC power supply for load sharing and redundancy. The power supplies are fully isolated, which eliminates a single point of power failure.

The CHP Max5000 switched-mode DC power supplies accepts DC input from -72 to -36 VDC and produces 475 W to power a fully-loaded chassis of application modules. Each chassis accepts a second backup DC power supply for load sharing and redundancy. These power supplies are fully isolated, eliminating a single point of power failure.

CHP power supplies are located on the far-right side of the chassis behind the Craft Management Module (CMM) or System Management Module (SMM). Isolated outputs allow the primary and redundant supplies to operate in a power-sharing configuration. Should the primary power source fail, a second power supply provides all necessary DC power.

*AC power supply with or without US power cord. International customers will need to order the power supply without the power cord and select the appropriate power cord for their application from the ordering matrix in the CHP System technical specification.

CHASSIS SPECIFICATIONS

Characteristics	Specification
Physical	
Chassis Dimensions	19 in W x 3.5 in H x 18 in D (48.3 cm x 8.9 cm x 45.7 cm)
Module Port Dimension, 1 Wide	1.25 in (3.2 cm)
Weight, Empty ¹	15.5 lb (7.0 kg)
Environmental	
Operating Temperature Range	0° to 50°C (32° to 122°F)
Storage Temperature Range	-40° to 70°C (-40° to 158°F)
Humidity	85% non-condensing (max)
Interfaces	
SNMP Interface ²	Connector: RJ-45; Electrical Interface: 10BaseT Ethernet
Hi Speed Shelf Interconnect Interface ³	Connector: RJ-45; Electrical Interface: 100BaseT Ethernet
Lo Speed Shelf Interconnect Interface	Connector: RJ-14; Electrical Interface: RS-485
Local Alarm Terminal Interface ⁴	Connector: Terminal block; Electrical Interface: NO, NC, or C

NOTES:

1. Chassis enclosure and backplane without modules.
2. Requires use of system management module (SMM).
3. High speed shelf interconnection only; requires backplane Ethernet Switch (P/N CHP-BP-ETH-SW).
4. Dry contact closures. NO = Normally Open. NC = Normally Closed. C = Common.

CHP-PS/AC1-SW AC POWER SUPPLY SPECIFICATIONS

Characteristics	Specification
Physical	
External Dimensions	3.9 in W x 1.57 in H x 14.46 in D (9.91 cm x 3.99 cm x 36.73 cm)
Weight	2.75 lb (1.24 kg)
Environmental	
Operating Temperature Range	0° to 50°C (32° to 122°F)
Storage Temperature Range	-40° to 70°C (-40° to 158°F)
Humidity	5% to 95% non-condensing
Power Requirements	
Input Voltage, 47 to 63 Hz	85 to 264 Vac
Input Current Limit, Continuous, RMS	9.0 A (max)
Inrush Current Limit, Peak	40 A (max)
Input Transient, IEEE C62.41-1991 Category B 1.2, 50 μs	4 kV/0.13 kA
Power Consumption	700 W (max)
Input Connector	IEC 320-C14 plug
Output Voltages and Current	12.0 Vdc +0.35/-0.0 Vdc, 2.3 to 24 A 5.0 Vdc +0.2/-0.05 Vdc, 31 A -5.0 Vdc +0.15/-0.2 Vdc, 2 A 3.5 Vdc ± 0.1 Vdc, 5 A
Output Noise Ripple, RMS	25 mV @ 12.0 V output 25 mV @ 5.0 V output 20 mV @ -5.0 V output 20 mV @ 3.5 V output
Efficiency	68% (min)
Power Factor	0.9
Status Interface	
Functions Monitored	All DC voltages, internal temperature, fan currents

CHP-PS/DC1-SW DC POWER SUPPLY SPECIFICATIONS

Characteristics	Specification
Physical	
External Dimensions	3.9 in W x 1.57 in H x 14.46 in D (9.91 cm x 3.99 cm x 36.73 cm)
Weight	2.75 lb (1.24 kg)
Environmental	
Operating Temperature Range	0° to 50°C (32° to 122°F)
Storage Temperature Range	-40° to 70°C (-40° to 158°F)
Humidity	5% to 95% non-condensing
Power Requirements	
Input Voltage	-72 to -36 Vdc
Input Current Limit	15.0 A @ 36 Vdc (max)
Inrush Current Limit ¹	40 A (max)
Power Consumption	540 W (max)
Input Connector	3-pin male connector, mates with power plug (P/N MT0401)
Output Voltages and Current	12.0 Vdc +0.35/-0.0 Vdc, 24 A 5.0 Vdc +0.2/-0.05 Vdc, 31 A -5.0 Vdc +0.15/-0.2 Vdc, 2 A 3.5 Vdc ± 0.1 Vdc, 5 A
Output Noise Ripple, RMS	25 mV @ 12.0 V output 25 mV @ 5.0 V output 20 mV @ -5.0 V output 20 mV @ 3.5 V output
Output Noise Switching Spikes, Peak to Peak	6100 mV @ 12.0 V output 100 mV @ 5.0 V output 60 mV @ -5.0 V output 60 mV @ 3.5 V output
Efficiency ²	85% (min)
Status Interface	
Functions Monitored	All DC voltages, internal temperature, fan currents
Regulatory Requirements³	
	UL60950 3rd Ed/CSA C22.2 number 60950 and EN60950
	EN50083-2
	EN300 386 V1.3.1
	FCC Part 15, Class A
	FCC Part 76, Subpart K
	EN55022, Class A

NOTES:

- Inrush current shall not trip a 20 A mains external circuit breaker during a Hot Start condition. Hot Start occurs when a thermally stabilized power supply is removed and immediately reinserted.
- When operating at 25°C over the input operating range with a full rated output load.
- All emissions tests must be passed in two configurations: two power supplies operating redundantly and a single power supply installed in a chassis configured to provide maximum system load.

ORDERING INFORMATION

Model Name	Component Type	Description
CHP-CHASSIS-19U	Chassis	19-inch CHP Max5000 chassis with enhanced backplane and slots for 10 application modules and 2 power supplies
CHP-CHASSIS-R-19U	Chassis	19-inch CHP Max5000 recessed chassis for use with front fiber applications, includes enhanced backplane and slots for 10 application modules and 2 power supplies
CHP-EXTBKT-23	23-in External Bracket	Bracket adapts 19-inch chassis to install in a 23-inch rack
CHP-PS/AC1-SW	Power Supply	Isolated 475 Watt power supply accepting 110/220 Vac input
CHP-PS/DC1-SW	Power Supply	Isolated 475 Watt power supply accepting -48 Vdc input

RELATED PRODUCTS

CHP Transmitters	Optical Patch Cords
CHP Receivers	Optical Passives
CHP Management Module	Installation Services

Contact Customer Care for product information and sales:

- United States: 866-36-ARRIS
- International: +1-678-473-5656

COMMScope®

Note: Specifications are subject to change without notice.

Copyright Statement: © 2022 CommScope, Inc. All rights reserved. ARRIS, the ARRIS logo, CORView, and CHP Max5000 are trademarks of CommScope, Inc. and/or its affiliates. All other trademarks are the property of their respective owners. No part of this content may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from CommScope, Inc and/or its affiliates ("CommScope"). CommScope reserves the right to revise or change this content from time to time without obligation on the part of CommScope to provide notification of such revision or change.

1514614_CHP Chassis and PS_DS_RevA