

CU8919-000 | FIST-SOSA2-4DC-S



FIST® Splice Sub-assembly kit with 4 foldable dual circuit trays, each for holding up to 2x2 primary coated fibers, with Heat Shrink type splice holder

- Splice sub-assemblies consists of a wraparound groove plate holding the included splice organizer trays
- Groove plates are designed with slots for routing fiber to and from the organizer trays
- Loop-back facility allowing for single circuit uncut looped fiber storage on the splice tray
- Compliant with most splice types and independent of any optical fiber construction

Product Classification

Regional Availability	EMEA
Product Type	Fiber splice tray
Product Brand	FIST®
Product Series	FIST-SOSA2

General Specifications

Application	For use with BUDI fiber wall boxes For use with FIST fiber splice closures For use with FIST fiber splice panels
Color	Gray
Splice Tray Chip Type	Heat shrink
Splice Tray Construction	DC (Foldable dual circuit tray for up to 4 primary coated fibers)
Splice Tray Included, quantity	4
Splices per Tray, quantity	4
Used UMS Units, quantity	1


Dimensions

Height	4 mm 0.157 in
Width	105 mm 4.134 in
Length	152 mm 5.984 in
Fiber Storage Length, maximum	1200 mm for 250 µm fibers
Fiber Storage Length, minimum	900 mm 35.433 in
Splice Protector Length, maximum	47 mm 1.85 in
Splice Protector Length, minimum	43 mm 1.693 in

CU8919-000 | FIST-SOSA2-4DC-S

Splice Protector Diameter, maximum	2.6 mm 0.102 in
Splice Protector Diameter, minimum	2.2 mm 0.087 in

Dimension Drawing



Material Specifications

Material Type	PBT PET
----------------------	-----------

Mechanical Specifications

Minimum Bend Radius, standard	25 mm 0.984 in
--------------------------------------	------------------

Environmental Specifications

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	93%, non-condensing
Environmental Space	Indoor Outdoor

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton
Weight, net	0.1 kg 0.22 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant



* Footnotes

Used UMS Units, quantity The overall space consumed in the Universal Mounting System (UMS) frame is expressed in UMS units. One UMS unit equals 6 mm.