

Universal Grounding Kit for 1/4 in through 5/8 in corrugated coaxial cable, 1 m

#### **Product Classification**

 Product Type
 Grounding kit

 Product Brand
 HELIAX®

Ordering Note ANDREW® standard product (Global)

### General Specifications

Bonding Conductor Jacketing MaterialPVCBonding Conductor MaterialCopperBonding Conductor Wire Size10 gauge

Cable Type Corrugated | Smoothwall

**Color** Black

**Grounding Kit Type**Universal Grounding Kits

Grounding Strap MaterialTinned copperLug AttachmentFactory attachedLug TypeOne-hole lug

Thread Size M8

#### Dimensions

Bonding Conductor Length990.6 mm | 39 inCable Jacketing Removal Length, maximum58.42 mm | 2.3 inCable Jacketing Removal Length, minimum55.88 mm | 2.2 inCompatible Diameter, maximum15.24 mm | 0.6 inCompatible Diameter, minimum2.54 mm | 0.1 in

**Nominal Size** 1/2 in | 1/4 in | 3/8 in | 5/8 in



# GK-SUNV-1M

## **Electrical Specifications**

**Current Handling** Tested to withstand 30,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

Grounding, Bonding and Shielding Test Method MIL-STD-188-124A

**Lightning Protection Test Method**IEC 1024-1

Material Specifications

**Blowing Rain Test Method** 

Rivet Material Copper

### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +80 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +176 \,^{\circ}\text{F})$ 

Corrosion Test Method MIL-STD-1344, Method 1001

Freezing Rain/Icing Test Method MIL-STD-810, Method 521

**Humidity Test Method** MIL-STD-1344, Method 1002

Immersion Test Method IEC 60529:2001, IP68

UV Resistance Test Method MIL-STD-810, Method 505

Vibration Test Method MIL-STD-202, Method 214

Weatherproofing Method Butyl and electric tape

Packaging and Weights

 Height, packed
 152.4 mm | 6 in

 Width, packed
 76.2 mm | 3 in

 Length, packed
 58.42 mm | 2.3 in

Included Grounding kit | Hardware | Lug | One roll of 2 in PVC tape | One

roll of 24 in butyl rubber tape

MIL-STD-810, Method 506

Packaging quantity 1

**Weight, gross** 0.28 kg | 0.617 lb

# Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ANDREW® an Amphenol company

# GK-SUNV-1M

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-71 - Black 2 in PVC Tape, 20 ft

#### \* Footnotes

**Grounding, Bonding and Shielding Test Method** Military Standard for Grounding, Bonding, and Shielding: Bond Resistance

Requirement of a Maximum dc resistance of 0.001 ohm

**Lightning Protection Test Method**Protection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02

