

# 760251048 | EPX-4U-MOD-ENC

---



EPX 4U sliding panel, accepts (16) G2 style splice cassettes, modules or adapter packs, providing up to 192 duplex LC ports

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel   Fiber patch/splice panel
<b>Product Series</b>	EPX

## General Specifications

<b>Application</b>	Accepts sixteen G2 modular cassettes
<b>Color</b>	Black
<b>Intelligence Type</b>	Not iPatch® ready
<b>Interface, front</b>	Unloaded
<b>Module/Adapter Pack Slots, quantity</b>	16
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	4
<b>Shelf Movement</b>	Sliding
<b>Total Fibers, quantity</b>	384
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	412.75 mm   16.25 in

## Environmental Specifications

<b>Safety Standard</b>	CSA 22.2   UL 1863
------------------------	--------------------

## Packaging and Weights

# 760251048 | EPX-4U-MOD-ENC

---

**Packaging quantity** 1  
**Weight, net** 7.439 kg | 16.4 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

