


6-2111976-3 | MP-5EMT-A-1



Modular Plug Kit, category 5e, shielded, 8-position, 4.7 – 5.5 mm max cable jack OD, 100/bag

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Modular plug

General Specifications

ANSI/TIA Category	5e
Cable Type	Round, shielded
Conductor Type	Solid Stranded
Interface	RJ45
Positions/Loaded Contacts	8/8
Termination Type	IDC

Dimensions

Compatible Cable Diameter, maximum	5.5 mm 0.217 in
Compatible Cable Diameter, minimum	4.7 mm 0.185 in
Compatible Insulated Conductor Diameter, maximum	1.09 mm 0.043 in
Compatible Insulated Conductor Diameter, minimum	0.89 mm 0.035 in
Contact Plating Thickness	1.27 µm
Compatible Conductor Gauge, solid	26–23 AWG
Compatible Conductor Gauge, stranded	26–23 AWG

Electrical Specifications

Insulation Resistance, minimum	500 mOhm
---------------------------------------	----------

Material Specifications

Contact Base Material	Phosphor Bronze
Contact Plating Material	Gold
Material Type	Glass filled polycarbonate
Plug Shield Base Material	Stainless steel
Plug Shield Plating Material	Nickel

Mechanical Specifications

Plug Insertion Life, minimum	750 times
-------------------------------------	-----------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	UL 1863

Packaging and Weights

Packaging quantity	100
Packaging Type	Bag Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

