


UDX1726Q-N10 | E11F03P87



Ultra-Compact Quad Diplexer PCS-AWS/BRS, DC/AISG on PCS-AWS, NEX10 Connectors

- Quad configuration, 4x4 MIMO ready
- Ideal for small cell applications
- dc/AISG pass-through on low frequency ports
- Industry leading PIM performance
- Miniature NEX10™ series connector for superior PIM and compact size

Product Classification

Product Type Diplexer

General Specifications

Color Gray

Common Port Label Common

Modularity 4-Quad

RF Connector Interface NEX10 Female

RF Connector Interface Body Style Long neck


Dimensions

Height 65 mm | 2.559 in

Width 140 mm | 5.512 in

Depth 46 mm | 1.811 in

Outline Drawing



Electrical Specifications

Impedance	50 ohm
License Band, Band Pass	AWS 1700 AWS 2000 PCS 1900 TDD 2600

Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through Method	Factory set
dc/AISG Pass-through Path	Branch 1
dc/AISG Pass-through, combiner	Branch 1
dc/AISG Pass-through, demultiplexer	Branch 1
Lightning Surge Current	5 kA
Lightning Surge Current Waveform	8/20 waveform
Voltage	10–30 Vdc

UDX1726Q-N10 | E11F03P87

Electrical Specifications, AISG

AISG Carrier	2.176 MHz ± 100 ppm
--------------	---------------------

Electrical Specifications

Sub-module	1 2 3 4	1 2 3 4
Branch	1	2
Port Designation	PCS-AWS	BRS (B41)
License Band	PCS 1900, Band Pass AWS 1700, Band Pass AWS 2000, Band Pass	TDD 2600, Band Pass

Electrical Specifications, Band Pass

Frequency Range, MHz	1695–2200	2496–2700
Insertion Loss, typical, dB	0.1	0.15
Total Group Delay, maximum, ns	15	15
Return Loss, minimum, dB	20	20
Isolation, minimum, dB	35	35
Input Power, RMS, maximum, W	70	70
Input Power, PEP, maximum, W	1500	1500
3rd Order PIM, maximum, dBc	-161	-161
3rd Order PIM Test Method	Two +43 dBm carriers	Two +43 dBm carriers

Material Specifications

Finish	Painted
--------	---------

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP67

Packaging and Weights

Included	Mounting hardware
Mounting Hardware Weight	0.13 kg 0.287 lb
Volume	0.42 L
Weight, without mounting hardware	1.17 kg 2.579 lb