


# 511828-000 | OCC1C-X-610-NNSEF



OCC1C CWDM, double mux/demux, 1611 nm starting wavelength, 0.9 mm cable, field installable

## OBSOLETE

This product was discontinued on: July 25, 2023

### Replaced By:

CP5781-000                      OCC1C CWDM, double mux/demux, 1611 nm starting wavelength, 0.250 mm cable, field  
OCC1C-X-610-NNNQF-US26    installable

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	CWDM component
<b>Product Series</b>	OCC1C

## General Specifications

<b>Device Type</b>	Component, rectangular
<b>Functionality</b>	Multiplexing
<b>Technology Type</b>	Thin film filter (TFF)
<b>Application</b>	For use in FOSC closures
<b>Circuits, quantity</b>	2
<b>Distribution Type</b>	2-channel CWDM
<b>Interface, Input</b>	Stub tail
<b>Interface, Output</b>	Stub tail
<b>Multiplexers, quantity</b>	2

## Dimensions

<b>Pigtail Length, Input</b>	2.5 m   8.202 ft
<b>Pigtail Length, Output</b>	2.5 m   8.202 ft
<b>Pigtail Diameter</b>	0.9 mm   0.035 in

## Optical Specifications

**Starting Wavelength** 1611 nm

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

