



Fiber Optic Power Reducing Build Out Attenuator, singlemode LC/UPC, 4dB, blue

- Designed to reduce or balance the power in passive optical networks
- Insertable between the connector and the adapter and therefore suited for distribution frames, cabinets and boxes
- High system flexibility because of wave-length independency and polarization insensitivity

## OBSOLETE

This product was discontinued on: April 13, 2020

### Replaced By:

CX8690-000  
OCAB-L1-04-B3

Fiber Optic Power Reducing Build Out Attenuator, singlemode LC/UPC, 4dB, blue

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Fiber attenuator
<b>Product Series</b>	OCAB

## General Specifications

<b>Color</b>	Blue
<b>Interface</b>	LC/UPC

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.652.D
<b>Attenuation Tolerance</b>	± 0.5 dB
<b>Attenuation, nominal</b>	4 dB
<b>Operating Wavelength</b>	1430 – 1625 nm
<b>Optical Power, maximum</b>	250 mW
<b>Return Loss, minimum</b>	50 dB

## Environmental Specifications

# E96107-000 | OCAB-L1-04-B3

---

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Storage Temperature** -40 °C to +80 °C (-40 °F to +176 °F)