T-10-UW-NFI6



Low PIM Termination 10 W Load, 340-6000 MHz

| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
|-----------------------|---|
| Product Type | Termination Load |

General Specifications

| Device Type | Termination Load |
|-----------------------|------------------|
| Application | Indoor |
| Color | Silver |
| Inner Contact Plating | Silver |
| Interface | N Female |
| Outer Contact Plating | Trimetal |
| Dimonsions | |

Dimensions

| Length | 141 mm 5.551 in |
|-------------------|-------------------|
| Diameter, maximum | 44 mm 1.732 in |

Electrical Specifications

| 3rd Order IMD | -163 dBc | |
|---------------------------|--|--|
| 3rd Order IMD Test Method | Two +40 dBm carriers | |
| Average Power, maximum | 10 W | |
| Impedance | 50 ohm | |
| Operating Frequency Band | 340 – 6000 MHz | |
| VSWR at Frequency Band | 1.2:1 @ 555-2700 MHz 1.3:1 @ 2700-6000 MHz 1.4 @ 340-555 MHz | |

Environmental Specifications

| Operating Temperature | -25 °C to +50 °C (-13 °F to +122 °F) |
|-----------------------|--------------------------------------|
| Relative Humidity | Up to 100% |

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 27, 2023



T-10-UW-NFI6

Packaging and Weights

| Height, packed | 65 mm 2.559 in |
|----------------|--------------------|
| Width, packed | 85 mm 3.346 in |
| Length, packed | 200 mm 7.874 in |
| Weight, gross | 0.6 kg 1.323 lb |
| Weight, net | 0.52 kg 1.146 lb |

Regulatory Compliance/Certifications

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Agency

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 27, 2023

