# JF-CAPKIT



Product Classification

### 2.2-5 Female End Cap Assembly


Product Type	Surge arrestor accessory
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product
General Specifications	
Interface	2.2-5 Female
Dimensions	
Height	18.1 mm   0.713 in
Width	18.1 mm   0.713 in
Length	19 mm   0.748 in

## Outline Drawing

Page 1 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025



#### 2,2-5 FEMALE END CAP ASSEMBLY

### Material Specifications

Finish	Trimetal
Material Type	Brass
Mechanical Specifications	
Coupling Nut Proof Torque	4 N-m   35.403 in lb
Interface Durability	50 cycles
Mechanical Shock Test Method	IEC 60068-2-27

#### **Environmental Specifications**

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Corrosion Test Method	IEC 60068-2-11
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68

Page 2 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

# JF-CAPKIT

Moisture Resistance Test Method	IEC 60068-2-3
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

#### Packaging and Weights

Packaging quantity	1
Weight, net	24.24 g   0.053 lb

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant
$\odot$	



Immersion Depth Immersion at specified depth for 24 hours

ANDREW

an Amphenol company

Page 3 of 3