# E14F06P46



Ultra Compact Quad Diplexer, 3400–3600/3700–4100 MHz, DC/AISG Bypass on low frequency port, with 4.3-10 connectors

- Industry leading PIM performance
- New 4.3-10 connectors for improved PIM performance and size reduction
- dc/AISG blocking on all ports
- New Combining Solution to introduce 5G, 3.5GHz band
- Compact form factor with reduced size and weight

#### **Product Classification**

Product Type Diplexer

#### General Specifications

ColorGrayModularity2-Twin

MountingPole | WallMounting Pipe HardwareBand clamps (2)

**RF Connector Interface** 4.3-10 Female

#### Dimensions

 Height
 92 mm | 3.622 in


 Width
 220 mm | 8.661 in

 Depth
 121 mm | 4.764 in

 Mounting Pipe Diameter Range
 42.6–122 mm

## Outline Drawing

# E14F06P46



### **Electrical Specifications**

**Impedance** 50 ohm

# Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through PathBranch 1dc/AISG Pass-through, combinerBranch 1dc/AISG Pass-through, demultiplexerBranch 1

# **Electrical Specifications**

 Sub-module
 1 | 2
 1 | 2

 Branch
 1
 2

**Port Designation** PORT 1 3400-3600 PORT 2 3700-4100

Page 2 of 3




# E14F06P46

# Electrical Specifications, Band Pass

Frequency Range, MHz	3400-3600	3700-4100
Insertion Loss, typical, dB	0.4	0.4
Return Loss, typical, dB	20	20
Isolation, typical, dB	35	35
Input Power, RMS, maximum, W	100	100
Input Power, PEP, maximum, W	1000	1000
3rd Order PIM, maximum, dBc	-150	-150
3rd Order PIM Test Method	Two +43 dBm carriers	Two +43 dBm carriers

## Block Diagram



### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$ 

**Corrosion Test Method** IEC 60068-2-11, 30 days

**Environmental Test Method** ETSI EN 300 019-1-4

**Ingress Protection Test Method**IEC 60529:2001, IP67

## Packaging and Weights

**Included** Mounting hardware

**Volume** 2.45 L

Weight, net  $4.8 \text{ kg} \mid 10.582 \text{ lb}$  Weight, without mounting hardware  $4.5 \text{ kg} \mid 9.921 \text{ lb}$ 

