UKJ600

Base Product



KJ-Series Modular Jack, RJ45, Cat6 Unshielded

Product Classification

Regional AvailabilityNorth AmericaPortfolioUniprise®Product TypeModular jackProduct SeriesUKJ Series

General Specifications

ANSI/TIA Category 6

Cable Type Unshielded

Conductor Type Solid | Stranded

Integrated Dust Cover Type None

Mounting Hubbell® faceplates | Leviton® faceplates | Panduit®

faceplates

Outlet Type Keystone

Termination Tool 110 Punchdown tool | SL Termination tool

Termination Type IDC

Transmission Standards ANSI/TIA-568-C.2 | ISO/IEC 11801 Class E

Wiring T568A | T568B

Dimensions

Compatible Conductor Gauge, solid24-22 AWGCompatible Conductor Gauge, stranded26-24 AWG

Electrical Specifications

 Contact Resistance Variation, maximum
 20 mOhm

 Contact Resistance, maximum
 100 mOhm

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface 1,500 Vac @ 60 Hz

COMMSCOPE®

UKJ600

Dielectric Withstand Voltage, RMS, contact-to-contact 1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 m0hm

Remote PoweringFully supports the safe delivery of power over LAN cabling

described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC

60512-99-002

PoE Durability Supports IEEE 802.3bt Type 4 (90 W) applications after 3000

plug to jack mating cycles

Material Specifications

Contact Plating Material Precious metals

Material Type Copper alloy | High-impact, flame retardant, thermoplastic

Termination Contact Plating Nickel

Mechanical Specifications

Plug Retention Force, minimum 133 N | 29.9 lbf

Plug to Jack Mating Cycles Complies to IEC 60603-7 series

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

