

BC-20-10



Pipe-to-Pipe Clamp, joins two 1-1/2 in to 3-1/2 in OD round members

Product Classification

Product Type Clamp set

General Specifications

Mounting Pipe-to-pipe

Taper Taper Tapered

Dimensions

Height 50.8 mm | 2 in

Width 152.4 mm | 6 in

Length 254 mm | 10 in

Mounting Diameter, maximum 88.9 mm | 3.5 in

Mounting Diameter, minimum 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

Weight, net 3.6 kg | 7.937 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted