



Mini-OPE 200-Series, Optical Terminal Enclosure, 6-port full-size connector, 1x8 splitter, black, wall mount

- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Functionality to splice and store feeder cable in the field with the possibility to splice in the field two extra branch cables
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and-play drop cable installations
- Integrated external cable fixation guarantees easy, fast and reliable cable manipulations

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America
Product Type	Access terminal, without splitter/tap
Product Series	Mini-OPE 200


General Specifications

Cable, quantity	0
Distribution Type	1 x 8 splitter
Enclosure Color	Black
Mounting	Handhole Pole Wall
Port Type	Hardened full-size SC/APC
Port, quantity	6
Split Ratio	Symmetrical
Splitter, quantity	1
Stub Type	No tail


Dimensions

Height	358.5 mm 14.114 in
Width	166 mm 6.535 in
Depth	129.3 mm 5.091 in

Dimension Drawing



Ordering Tree



Material Specifications

Enclosure Material Type Glass filled polypropylene (GF-PP)

Optical Specifications

Fiber Type G.652.D

Wavelength Range 1260–1635 nm

Insertion Loss, Terminal Connector, maximum 0.4 dB

760245212 | OTE200-06MH-18-S12-B-W

Insertion Loss, Terminal Connector, typical	0.16 dB
Return Loss, Connector, minimum	65 dB

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–100%, condensing
Environmental Space	Above ground Below ground Buried
Qualification Standards	IEC 60529, IP68 + 3 m waterhead
UV Resistance	UV stabilized

Packaging and Weights

Included	Cable termination unit (2) Enclosure (1) Fiber pigtail cassette (1) Splice Cassette (2)
Packaging quantity	1
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted



Included Products

CW8094-002 – TENIO™ Cable Termination Unit kit
TENIO-CTU-L-(10)