RCPB-1K4PUE03100



RapidFiber® Termination Panel, 48-Position 1RU, singlemode, LC/UPC to MPO, 31 m

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with rapid cable
Product Brand	RapidFiber®
Product Series	RCP

General Specifications

Functionality	Patching
Body Style	Symmetrical
Cable Exit Location	Rear, left side
Cable Stub Type	Indoor, microcable
Color	Black
Door Type, front	Hinged Slide latch Transparant
Growth Configuration	Fully loaded
Interface, front	LC
Interface Feature, front	Standard
Interface, rear	MPO
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 19 in EIA 23 in
Rack Units	1
Shelf Movement	Sliding
Total Fibers, quantity	48
Total Ports, quantity	48
Transmission Standards	IEC 60794-2 ISO/IEC 11801 TIA/EIA-568-B.3
Dimensions	

Height

44.45 mm | 1.75 in

Page 1 of 3


©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: October 18, 2021



RCPB-1K4PUE03100

Width	482.6 mm 19 in
Depth	381 mm 15 in
Cable Stub Length	31 m 101.706 ft

Ordering Tree



Material Specifications

Finish	Powder coated
Material Type	Steel
Optical Specifications	

Fiber Mode	Singlemode
Fiber Type	G.652.D G.657.A2/B2

Page 2 of 3

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: October 18, 2021



RCPB-1K4PUE03100

Environmental Specifications

Operating Temperature	-5 °C to +55 °C (+23 °F to +131 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%-85%, non-condensing
Qualification Standards	NEBS Level 3 Telcordia GR-1435 Telcordia GR-326 Telcordia GR-409 UL 1863

Packaging and Weights

1

Packaging quantity

Page 3 of 3

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: October 18, 2021

