

# 760249179 | 26" Pole Cab with 12" Integrated Pole Shaft



Decorative Pole Cab with an Integrated Pole supporting 4G/5G/mmWave technologies as well as smart devices

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Also available with a 30"x30" base for additional capacity  
-Multi Carrier capable

**OBSOLETE**

## Product Classification

<b>Product Type</b>	Pole cab
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	ANDREW® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)
<b>Compatible Foundation Type</b>	Poured Concrete   Pre-Cast Concrete
<b>Compatible Smart Devices</b>	Cameras   Digital Signage   Emergency Call Station   Environmental Monitoring   Security Lighting   WIFI
<b>Cooling</b>	Fan Cooling
<b>Power Supply Compatibility</b>	DELTA 2.0   PSU-AC-08
<b>Radio Compatibility, Ericsson</b>	(1) 8843/4449 dual-band high power radio and (2) PSU-AC08   1281   220x   440x   4426   4478   6701
<b>Radio Compatibility, Nokia</b>	AEUB   AEWB   AEWD /AEWE   AHFB   AHFIA   AHFIB   AHIA   AHIB   AHLBA   AHLBBA   AZRB
<b>Radio Compatibility Samsung</b>	AT1K01   AT1K02   AT1K0X   DELTA 2.0   Diplexer   HT1K01   Power Distribution   RF4402D-D1A   RFV01U-D1A   RFV01U-D2A   RT2201-46A   RT4401-48A
<b>Radios Included</b>	None

# 760249179 | 26" Pole Cab with 12" Integrated Pole Shaft

---

## Dimensions

<b>Height Note</b>	4 ft tall Equipment Cabinet Base
<b>Pole Height Options</b>	7.925 m   26 ft
<b>Width</b>	660.4 mm   26 in
<b>Depth</b>	660.4 mm   26 in
<b>Depth Note</b>	Square
<b>Pole Diameter</b>	323.85 mm   12.75 in

## Electrical Specifications

<b>Power/Fiber Input</b>	AC load center with OVP and disconnect
--------------------------	--

## Material Specifications

<b>Finish Aluminum</b>	Chromate
<b>Finish Concealment Covers</b>	Powder coated
<b>Material Type</b>	Galvanized steel

## Environmental Specifications

<b>Thermal Compliance</b>	GR-487
---------------------------	--------