

SSC-760236114N | Radio Enclosure for Nokia Radios



Middle of Pole Pico Concealment Enclosure for Nokia Radios

- Intended to be used with remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

SSC-760236114N2x
Up to (4) AirScale Micro Radios

SSC-760236114N3x
(1) Nokia Dual Band 160W Radio & (1) AirScale Micro Radio
or
(1) AHFIB & (1) DC Rectifier (Nokia FPAE OR Delta 1kW or 1.8kW)

Includes Standard Mounting kit for through bolt, clamp, and banding

Product Classification

Product Type	Mid pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Power Supply Compatibility	DELTA 2.0
Radio Compatibility, Nokia	(1) Airscale Dual Band 160W + (1) AirScale micro radio AHFIA AHFIB Power Distribution Up to (4) AirScale micro radios
Radios Included	None

Dimensions

Height 1016 mm | 40 in

SSC-760236114N | Radio Enclosure for Nokia Radios

Width 401.32 mm | 15.8 in

Depth 304.8 mm | 12 in

Electrical Specifications

Power/Fiber Input Trade size knockouts at rear side

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.125 m³ | 4.4 ft³

Weight (loaded) 36.287 kg | 80 lb

Weight (unloaded) 18.144 kg | 40 lb