FHD-JJ1D



Fiber Optic Drop Cable Assembly, SC/APC to SC/APC, universal flat locatable/tonable

- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Hardened drop cables incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber drop cable assembly

Product Series FHD

Ordering Note Drops are automatically coiled 0 to 1,000 ft (305 m), unless spool option "L" or "R" is

specified for this range of length | Drops are automatically spooled at 1,001 ft (306

m) with connector B deploying first from spool

General Specifications

Cable Type Locatable - Universal Flat

Connector A, quantity

Color, boot AGreenColor, connector AGreenConnector B, quantity1

Color, boot B Green
Color, connector B Green

Interface, Connector A SC/APC with pulling sock

Interface, Connector B SC/APC

Jacket Color Black

Total Fibers, quantity 1

Transmission Standards IEC 61753-1 | IEC 61754-4 | IEC 61755

Dimensions

Cable Assembly Length Range (m) 1 - 750

COMMSCOPE®

FHD-JJ1D


Cable Assembly Length Range (ft)

50 - 2000

Cable Outer Diameter

4.6 x 7.4 mm (0.18 x 0.29 in)

Ordering Tree



- Cable Type K not available with LC & SC Options

- **Cable Length shown as an example, additional cable lengths available upon request up to 2,000 ft. (600 m).


 **Special Request Feature not available with cable types K.

 Drops are automatically coiled 0 to 1,000 ft. unless "L" or "R" is specified for this range of length.

 Drops are automatically spooled at 1,001 ft. with Connector B deploying first from spool. Add "L" to lengths over 1,001 ft. if Connector A needs to deploy first.

 ****Includes pulling sock 25 lbs. of pulling force

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded 91.44 mm | 3.6 in Minimum Bend Radius, unloaded 63.5 mm | 2.5 in Tensile Load, long term, maximum 400.34 N | 90 lbf 1,334.466 N | 300 lbf Tensile Load, short term, maximum Cable Crush Resistance, maximum 44 N/mm | 251.246 lb/in

Page 2 of 3

FHD-JJ1D

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Insertion Loss, maximum, connector A0.4 dBInsertion Loss, maximum, connector B0.4 dBReturn Loss, minimum, connector A65 dBReturn Loss, minimum, connector B65 dB

Environmental Specifications

Installation temperature-30 °C to +60 °C (-22 °F to +140 °F)Operating Temperature-40 °C to +70 °C (-40 °F to +158 °F)Storage Temperature-40 °C to +75 °C (-40 °F to +167 °F)

Environmental Space Outdoor, buried

Jacket UV Resistance UV stabilized

Qualification Standards NEMA type 6, 10 ft waterhead | Telcordia GR-20 | Telcordia GR-3120

Packaging and Weights

Cable weight 36 kg/km | 24.191 lb/kft

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant

