
760252048 | 0-144-LA-8Z-M12BK/22G/093



Fiber OSP cable, PE, Loose Tube Gel-filled CST, 144 fiber, Singlemode G. 652.D and G.657.Al, Meters jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series O-LA

General Specifications

Cable Type Stranded loose tube

Construction Type Armored
Subunit Type Gel-filled
Jacket Color Black
Jacket Marking Meters
Fibers per Subunit, quantity 12

Dimensions

Total Fiber Count


Buffer Tube/Subunit Diameter 2.2 mm | 0.087 in Diameter Over Jacket 12.2 mm | 0.48 in

144

Representative Image



760252048 | 0-144-LA-8Z-M12BK/22G/093



Mechanical Specifications

Minimum Bend Radius, loaded 240 mm | 9.449 in Minimum Bend Radius, unloaded 120 mm | 4.724 in Tensile Load, short term, maximum 2700 N | 606.984 lbf

Compression 22 N/mm | 125.623 lb/in

IEC 60794-1-2 E3 **Compression Test Method**

Flex 25 cycles

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-21 E1

Optical Specifications

Fiber Type G.652.D and G.657.A1 | OS2

Optical Specifications, Wavelength Specific

0.22 dB/km @ 1,550 nm | 0.36 dB/km @ 1,310 nm Attenuation, maximum

Environmental Specifications

-10 °C to +60 °C (+14 °F to +140 °F) Installation temperature -40 °C to +70 °C (-40 °F to +158 °F) **Operating Temperature Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F) Buried | Ducted | Outdoor

Environmental Space

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5B

Page 2 of 3

760252048 | 0-144-LA-8Z-M12BK/22G/093

Environmental Test Specifications

Temperature Cycle -30 °C to +70 °C (-22 °F to +158 °F)

Temperature Cycle Test Method IEC 60794-1-2 F1

Packaging and Weights

Cable weight 140 kg/km | 94.076 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

