SHK-78-1-P



Single Hanger Kit for 7/8 in coaxial cable, single stack; includes hardware and angle adapter

Product Classification

Material Type

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	CommScope® non-standard product
General Specifications	
Cables per Hanger	1
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware
Dimensions	
Maximum Stack Height	1
Height	50.8 mm 2 in
Width	26.2 mm 1.031 in
Length	60.2 mm 2.37 in
Compatible Cable Diameter Range	26.7-28.2 mm
Compatible Diameter, maximum	28.2 mm 1.11 in
Compatible Diameter, minimum	26.7 mm 1.051 in
Nominal Size	7/8 in
Electrical Specifications	
Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB
Material Specifications	

Engineered plastic

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2024



SHK-78-1-P

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
Environmental Specifications	
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degredation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Packaging and Weights	

Height, packed	15 cm 5.906 in
Width, packed	15 cm 5.906 in
Length, packed	3 cm 1.181 in
Included	Angle adapter Hardware
Packaging quantity	1
Weight, gross	0.45 kg 0.992 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2024

