


NNH4S4-65D-R7



20-port sector antenna, 4x 698–896, 8x 1695–2360 MHz, 65° HPBW and 8x 3400–4000 MHz, 90° HPBW, 7x RET

- Multi-band FDD antenna featuring C-Band 8T8R functionality
- The C-band RET is factory set to AISG2. All other RET are assigned to AISG1
- Feature the same dimensions as existing 8 and 12-port FDD capable antennas
- New endcap designs provide improved wind loading performance

General Specifications

Antenna Type	Sector- and beamforming
Band	Multiband
Calibration Connector Interface	4.3-10 Female
Calibration Connector Quantity	1
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, high band	8
RF Connector Quantity, mid band	8
RF Connector Quantity, low band	4
RF Connector Quantity, total	20



Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	2 female 2 male
Input Voltage	10–30 Vdc
Internal RET	High band (1) Low band (2) Mid band (4)
Power Consumption, active state, maximum	8 W

NNH4S4-65D-R7

Power Consumption, idle state, maximum	1 W
Protocol	3GPP/AISG 2.0 (Multi-RET)
Dimensions	
Width	498 mm 19.606 in
Depth	197 mm 7.756 in
Length	2688 mm 105.827 in
Net Weight, without mounting kit	57 kg 125.663 lb
TDD Column Spacing	41 mm 1.614 in

Array Layout




Array ID	Frequency (MHz)	RF Connector	RET (MRET)	AISG No.	AISG RET UID
R1	698-896	1 - 2	1	AISG1	CPxxxxxxxxxxxxMM.1
R2	698-896	3 - 4	2	AISG1	CPxxxxxxxxxxxxMM.2
Y1	1695-2360	5 - 6	3	AISG1	CPxxxxxxxxxxxxMM.3
Y2	1695-2360	7 - 8	4	AISG1	CPxxxxxxxxxxxxMM.4
Y3	1695-2360	9 - 10	5	AISG1	CPxxxxxxxxxxxxMM.5
Y4	1695-2360	11 - 12	6	AISG1	CPxxxxxxxxxxxxMM.6
P1	3400-4200	13 - 20	7	AISG2	CPxxxxxxxxxxxxMM.1

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration

NNH4S4-65D-R7



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2360 MHz 3400 – 4000 MHz 698 – 896 MHz
Polarization	±45°
Total Input Power, maximum	900 W @ 50 °C

Electrical Specifications

Frequency Band, MHz	698-806	806-896	1695-1880	1850-1990	1920-2180	2300-2360	3400-3800	3700-4000
Gain, dBi	15.8	16.5	16.4	17.2	17.8	18	16.4	16.6
Beamwidth, Horizontal, degrees	70	63	73	66	61	58	86	73
Beamwidth, Vertical, degrees	8.8	7.8	6.1	5.8	5.5	5	6.1	5.8
Beam Tilt, degrees	2-12	2-12	2-12	2-12	2-12	2-12	0-10	0-10
USLS (First Lobe), dB	16	16	16	17	17	17	15	15
Front-to-Back Ratio at 180°, dB	29	29	33	31	31	33	28	29
Coupling level, Amp, Antenna port to Cal port, dB							26	26

NNH4S4-65D-R7

Coupling level, max Amp Δ , Antenna port to Cal port, dB							± 2	± 2
Coupler, max Amp Δ , Antenna port to Cal port, dB							0.9	0.9
Coupler, max Phase Δ , Antenna port to Cal port, degrees							7	7
Isolation, Cross Polarization, dB	25	25	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25	25	25
Isolation, Co-polarization, dB							19	19
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-145	-145
Input Power per Port at 50°C, maximum, watts	300	300	250	250	250	250	75	75

Electrical Specifications, BASTA

Frequency Band, MHz	698–806	806–896	1695–1880	1850–1990	1920–2180	2300–2360	3400–3800	3700–4000
Gain by all Beam Tilts, average, dBi	15.6	16.2	15.8	16.8	17.3	17.7	15.6	15.9
Gain by all Beam Tilts Tolerance, dB	± 0.6	± 0.3	± 0.8	± 0.6	± 0.8	± 0.6	± 0.9	± 0.8
Beamwidth, Horizontal Tolerance, degrees	± 4.7	± 3.6	± 7.5	± 7.8	± 7.2	± 3.2	± 3.4	± 2.2
Beamwidth, Vertical Tolerance, degrees	± 0.6	± 0.5	± 0.4	± 0.3	± 0.4	± 0.3	± 0.4	± 0.4
USLS, beampeak to 20° above beampeak, dB	15	14	14	16	15	16	13	12
Front-to-Back Total Power at 180° \pm 30°, dB	23	24	25	24	26	27	21	21
CPR at Boresight, dB	25	28	21	24	24	21	14	14
CPR at Sector, dB	13	11	8	5	5	8	6	6

Electrical Specifications, Broadcast 65°

Frequency Band, MHz	3400–3800	3700–4000
Gain, dBi	18	18.7
Beamwidth, Horizontal, degrees	73	65
Beamwidth, Vertical, degrees	6.1	5.8
Front-to-Back Total Power at	24	25

NNH4S4-65D-R7

180° ± 30°, dB

USLS (First Lobe), dB

16 17

Electrical Specifications, Envelope Pattern

Frequency Band, MHz

3400–3800 3700–4000

Gain, dBi

21 21.2

Electrical Specifications, Service Beam

Frequency Band, MHz

3400–3800 3700–4000

Steered 0° Gain, dBi

20.8 21.1

Steered 0° Beamwidth,
Horizontal, degrees

25 26

Steered 0° Front-to-Back
Total Power at 180° ± 30°, dB

30 30

Steered 0° Horizontal
Sidelobe, dB

14 14

Steered 0° USLS (First Lobe),
dB

17 17

Steered 30° Gain, dBi

19.8 20.5

Steered 30° Beamwidth,
Horizontal, degrees

30 25

Steered 30° Front-to-Back
Total Power at 180° ± 30°, dB

26 27

Electrical Specifications, Soft Split

Frequency Band, MHz

3400–3800 3700–4000

Gain, dBi

19.8 20.2

Beamwidth, Horizontal,
degrees

30 27

Front-to-Back Total Power at
180° ± 30°, dB

27 27

Horizontal Sidelobe, dB

15 15

USLS (First Lobe), dB

16 16

Mechanical Specifications

Effective Projective Area (EPA), frontal

0.91 m² | 9.795 ft²

Effective Projective Area (EPA), lateral

0.29 m² | 3.122 ft²

Wind Loading @ Velocity, frontal

970.0 N @ 150 km/h (218.1 lbf @ 150 km/h)

Wind Loading @ Velocity, lateral

304.0 N @ 150 km/h (68.3 lbf @ 150 km/h)

NNH4S4-65D-R7

Wind Loading @ Velocity, maximum	1,162.0 N @ 150 km/h (261.2 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	667.0 N @ 150 km/h (149.9 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	565 mm 22.244 in
Depth, packed	368 mm 14.488 in
Length, packed	2874 mm 113.15 in
Weight, gross	78.9 kg 173.945 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant



Included Products

BSAMNT-4	-	Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.
BSAMNT-M4	-	Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---