

SSC-760248838 | Radio Enclosure for Nokia or Ericsson



Middle of Pole Pico Concealment Enclosure for Ericsson and Nokia Radios

- Intended to be used with remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

Ericsson: SSC-760248838E5X

(1) 4455 and (1) 4435 radios, (1) OAD-9 and (2) Diplexers

Nokia: SSC-760248838N3X

(1) AHFIA or AHFIB and (1) AWHHF radios, (1) POD-8, (1)

Rectifier and (2) Diplexer

Product Classification

Portfolio	CommScope®
Product Type	Mid pole
Product Brand	Metro Cell
Ordering Note	CommScope® standard product with terms
Warranty	One year

General Specifications

Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Pure White Umbra Grey (RAL 7022)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Power Supply Compatibility	APAF APAM DELTA 2.0 FPAE
Radio Compatibility, Ericsson	4435 4455
Radio Compatibility, Nokia	AHFIA AHFIB AWHHF
Radios Included	None

Dimensions

Height	937.26 mm 36.9 in
Width	424.18 mm 16.7 in

SSC-760248838 | Radio Enclosure for Nokia or Ericsson

Depth 363.22 mm | 14.3 in

Electrical Specifications

Power/Fiber Input Trade size knockouts at rear side

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.14 m³ | 4.95 ft³

Weight (loaded) 79.379 kg | 175 lb

Weight (unloaded) 24.948 kg | 55 lb

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines