## UJXQXUCTU

#### **Base Product**



Ultra Low Loss (ULL) OM4 MPO8 (Pinned) to unconnectorized, Fiber Trunk Cable Assembly,64-Fiber, Dual Rated (OFNR/LSZH)

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

## General Specifications

Connector A, quantity 8

Color, boot AGrayColor, connector AAquaConnector B, quantity0

Construction Type Stranded
Furcation Color Aqua

Interface, Connector A MPO-08/UPC Male

Interface, Connector B Unterminated

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 64

Dimensions

Breakout Length 22 in

Cable Assembly Length Range (m) 3 - 305


Cable Assembly Length Range (ft) 10 - 999

Page 1 of 8



# UJXQXUCTU

## Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

**Optical Specifications** 

Fiber Mode Multimode

**Fiber Type** OM4, LazrSPEED®

## **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C to } +60 \,^{\circ}\text{C (+14 °F to } +140 \,^{\circ}\text{F)}$ 

Environmental Space Dual Rated LSZH/Riser | Indoor

### Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



#### Included Products

760248167 N-064-MP-5K-F08AQ/20T/D Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 64 fiber multi-unit with 8 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color,

Page 2 of 8




# UJXQXUCTU

Dca flame rating

860659018 - MPO-08, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 2mm

# 760248167 | N-064-MP-5K-F08AQ/20T/D



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 64 fiber multi-unit with 8 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, Dca flame rating

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

**Jacket Color** Aqua

**Jacket Marking** Feet

Subunit, quantity 8

Fibers per Subunit, quantity 8

Total Fiber Count 64

**Dimensions** 

**Buffer Tube/Subunit Diameter** 2 mm | 0.079 in

**Diameter Over Jacket** 9.3 mm | 0.366 in

Representative Image



# 760248167 | N-064-MP-5K-F08AQ/20T/D



### Mechanical Specifications

Minimum Bend Radius, loaded 139 mm | 5.472 in

Minimum Bend Radius, unloaded 93 mm | 3.661 in

**Tensile Load, long term, maximum** 200 N | 44.962 lbf

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 233 m | 764.436 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

## **Environmental Specifications**

Installation temperature0 °C to +60 °C (+32 °F to +140 °F)Operating Temperature0 °C to +70 °C (+32 °F to +158 °F)Storage Temperature-40 °C to +70 °C (-40 °F to +158 °F)

Page 5 of 8



# 760248167 | N-064-MP-5K-F08AQ/20T/D

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Rating\$1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

1666 | UL 1685

**Environmental Test Specifications** 

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend0 °C to +60 °C (+32 °F to +140 °F)Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11Temperature Cycle0 °C to +70 °C (+32 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 74.5 kg/km | 50.062 lb/kft

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



## 860659018



#### MPO-08, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 2mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorAquaColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Male

Interface Feature Pinned

Total Fiber Count 8

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

**Optical Specifications** 

Fiber ModeMultimodeFiber TypeOM3 | OM4

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, ULL, maximum0.2 dBReturn Loss, minimum27 dB

Packaging and Weights

**COMMSCOPE®** 

# 860659018

#### **Packaging quantity**

1

## Regulatory Compliance/Certifications

Agency Cla	assification
------------	--------------

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

