

JM-CAPKIT



2.2-5 Male End Cap Assembly

Product Classification

Product Type	Surge arrester accessory
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications


Interface	2.2-5 Male
------------------	------------

Dimensions

Height	13.96 mm 0.55 in
Width	13.96 mm 0.55 in
Length	22.5 mm 0.886 in

Outline Drawing

JM-CAPKIT



Material Specifications

Finish	Trimetal
Material Type	Brass

Mechanical Specifications

Coupling Nut Proof Torque	4 N-m 35.403 in lb
Interface Durability	50 cycles
Mechanical Shock Test Method	IEC 60068-2-27

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Corrosion Test Method	IEC 60068-2-11
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68

JM-CAPKIT

Moisture Resistance Test Method	IEC 60068-2-3
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

Packaging and Weights

Packaging quantity	1
Weight, net	18.36 g 0.04 lb

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

* Footnotes

Immersion Depth	Immersion at specified depth for 24 hours
------------------------	---