

Fiber indoor/outdoor cable, TeraSPEED® Plenum Distribution, 6 fiber single-unit, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series P-OD

General Specifications

 Cable Type
 Distribution

 Construction Type
 Non-armored


Jacket ColorBlackJacket MarkingFeetTotal Fiber Count6

Dimensions

Diameter Over Jacket 5.4 mm | 0.213 in

Representative Image





Mechanical Specifications

Minimum Bend Radius, loaded81 mm | 3.189 inMinimum Bend Radius, unloaded54 mm | 2.126 inTensile Load, long term, maximum400 N | 89.924 lbfTensile Load, short term, maximum1335 N | 300.12 lbf

 Compression
 22 N/mm | 125.623 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 100 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED®

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

COMMSCOPE®

Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-104-696 | Telcordia GR-20 (water penetration) | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFNP (ETL) and c(ETL)
Flame Test Method NFPA 130 | NFPA 262

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze Test Method IEC 60794-1 F15

Heat Age $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Heat Age Test Method IEC 60794-1 F9

Low High Bend -40 °C to +70 °C (-40 °F to +158 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \left(-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F}\right)$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 28 kg/km | 18.815 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-8W-TB - TeraSPEED® Singlemode Fiber



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable