

760253648 | 26" Pole Cab with Tapered Fluted Shaft



Bottom of the Pole, 26in Square base with round tapered fluted shaft 4G /5G/mmWave Concealment Enclosure to house and conceal multiple low to high power radios and other wireless infrastructure equipment in a cabinet at the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Supports 4G and mmWave/5G mounting
Decorative arm and light not included

OBSOLETE

Replaced By:

760253649

30" Pole Cab with Tapered Fluted Shaft

Bottom of the Pole 30in Square base with round tapered fluted shaft 4G/5G/mmWave Concealment Enclosure to house and conceal multiple low to high power radios and other wireless infrastructure equipment in a cabinet at the base of the pole.

Product Classification

Product Type	Pole cab
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Color Options	Black (RAL 9005)
Compatible Foundation Type	Poured Concrete Pre-Cast Concrete
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting WIFI
Cooling	Fan Cooling
Power Supply Compatibility	ABB CC1600 CCI PSU-1200W-48-N DELTA 2.0 PSU-AC-08
Radio Compatibility, Ericsson	(1) 8843/4449 dual-band high power radio and (2) PSU-AC08 220x 440x
Radio Compatibility, Nokia	AHFIA AHFIB AHIA AHIB AHLBA AHLBBA AZRB Airscale micro
Radio Compatibility Samsung	RF4402D-D1A RT2201-46A RT4401-48A

760253648 | 26" Pole Cab with Tapered Fluted Shaft

Radios Included None

Dimensions

Height Note 4 ft tall Equipment Cabinet Base

Pole Height Options 8.839 m | 29 ft

Width 660.4 mm | 26 in

Depth 660.4 mm | 26 in

Depth Note Square

Pole Diameter 203.2 mm | 8 in

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect | Fiber demarcation

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Galvanized steel | Steel

Environmental Specifications

Thermal Compliance GR-487