760254315 | N-024-MP-8G1-F08YL/20T/B2



Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 24 fiber with 2.0 mm Subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Fiber Type, quantity 24
Fibers per Subunit, quantity 8

Filler, quantity 1

Jacket ColorYellowJacket MarkingFeetSubunit TypeGel-free

Subunit, quantity 3

Total Fiber Count 24

Dimensions

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket7.8 mm | 0.307 in

Mechanical Specifications

Minimum Bend Radius, loaded116 mm4.567 inMinimum Bend Radius, unloaded78 mm3.071 in

COMMSCOPE®

760254315 | N-024-MP-8G1-F08YL/20T/B2

Tensile Load, long term, maximum 200 N | 44.962 lbf

Tensile Load, short term, maximum 667 N | 149.948 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 340 m | 1,115.486 ft

Optical Specifications

Fiber Type G.657.A2/B2

Environmental Specifications

Installation temperature0 °C to +60 °C (+32 °F to +140 °F)Operating Temperature0 °C to +70 °C (+32 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Cable Qualification StandardsANSI/ICEA S-83-596Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2

Environmental Test Specifications

Low High Bend0 °C to +70 °C (+32 °F to +158 °F)Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11Temperature Cycle0 °C to +70 °C (+32 °F to +158 °F)



760254315 | N-024-MP-8G1-F08YL/20T/B2

Temperature Cycle Test Method

FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 60.1 kg/km | 40.385 lb/kft

Included Products

CS-8G1-MP – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T

G.657.A2, B2)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



CS-8G1-MP

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G. 657.A2, B2)

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±0.3 µm Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm Core/Clad Offset, maximum $0.5 \, \mu m$

Proof Test 689.476 N/mm² | 100000 psi

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 15 mm Ø mandrel, 1 turn
 0.50 dB @ 1,550 nm
 | 1.00 dB @ 1,625 nm

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.10 dB @ 1,550 nm
 | 0.20 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.03 dB @ 1,550 nm
 | 0.10 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

COMMSCOPE®

CS-8G1-MP

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1302 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.40 dB/km @ 1,310 nm | 0.40 dB/km @ 1,385

nm | 0.40 dB/km @ 1,550 nm | 0.50 dB/km @ 1,625

nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

 Mode Field Diameter
 8.6 μm @ 1,310 nm | 9.8 μm @ 1,550 nm

Mode Field Diameter Tolerance $\pm 0.4 \, \mu \text{m} \ @ \ 1310 \, \text{nm} \quad | \quad \pm 0.5 \, \mu \text{m} \ @ \ 1550 \, \text{nm}$

Polarization Mode Dispersion Link Design Value, maximum 0.06 ps/sqrt(km)

Standards Compliance ITU-T G.657.A2 | ITU-T G.657.B2

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

Temperature Dependence, maximum0.05 dB/kmTemperature Humidity Cycling, maximum0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

COMMSCOPE®