

F4A-HPHRHR

Base Product



HELIAX® 1/2 SureFlex® Jumper with interface types 4.3-10 Male Right Angle and 4.3-10 Male Right Angle

Product Classification

Product Type	SureFlex® Premium, static PIM
Product Series	RSJ4-50

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Right angle
Body Style, Connector B	Right angle
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	B

Dimensions

Cable Assembly Length Range (m)	1 – 15
Nominal Size	1/2 in

Electrical Specifications

3rd Order IMD Static	-119 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers per IEC 62037
DTF, Connector A	-34 dB
DTF, Connector B	-34 dB

Jumper Assembly Sample Label

F4A-HPHRHR



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition