

TA-XMHF



NEX10 Male to 4.3-10 Female Adapter

Product Classification

Product Type Adapter

General Specifications

Body Style Straight

Inner Contact Plating Silver

Interface NEX10 Male

Interface 2 4.3-10 Female

Outer Contact Plating Trimetal


Dimensions

Length 40.1 mm | 1.579 in

Diameter 20 mm | 0.787 in

Outline Drawing

TA-XMHF



Electrical Specifications

3rd Order IMD at Frequency	-119 dBm @ 1900 MHz
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss, maximum	0.05 dB
Connector Impedance	50 ohm
dc Test Voltage	1500 V
Inner Contact Resistance, maximum	2 mOhm
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 6000 MHz
Outer Contact Resistance, maximum	1 mOhm
Peak Power, maximum	0.1 kW
RF Operating Voltage, maximum (vrms)	1000 V
Shielding Effectiveness	110 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0-3000 MHz	1.052	32

TA-XMHF

3000–6000 MHz

1.106

26

Mechanical Specifications

Coupling Nut Torque	1.5 N-m 13.276 in lb
Coupling Nut Proof Torque	5 N-m 44.254 in lb
Coupling Nut Proof Torque Method	IEC 61169-1:9.3.6
Coupling Nut Retention Force	450 N 101.164 lbf
Coupling Nut Retention Force Method	IEC 61169-1:9.3.11
Insertion Force	35 N 7.868 lbf
Interface Durability	100 cycles
Mechanical Shock Test Method	IEC 60068-2-27

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F
Average Power, Inner Conductor Temperature	100 °C 212 °F
Climatic Sequence Test Method	IEC 60068-1
Corrosion Test Method	IEC 60068-2-11
Damp Heat Steady State Test Method	IEC 60068-2-3
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

Packaging and Weights

Weight, net	33.1 g 0.073 lb
--------------------	-------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

TA-XMHF

UK-ROHS

Compliant/Exempted



* Footnotes

Immersion Depth

Immersion at specified depth for 24 hours