


# 760255364 | C-096-LA-8W-M12BK/20G/GRP/D



Indoor/outdoor fiber cable, TeraSPEED® Single Jacket/Single GRP Armor, Gel-filled, Stranded Loose Tube, Singlemode OS2, black Provides Rodent Resistance.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-LA


## General Specifications

<b>Armor Type</b>	Non-metallic rods
<b>Cable Type</b>	Stranded loose tube
<b>Construction Type</b>	Armored
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE OS2 SM 96 FIBER EN50575 CLASS Dca [SERIAL NUMBER] [MM/YY] [METRE MARK]
<b>Subunit, quantity</b>	8
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	96

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	2 mm   0.079 in
<b>Diameter Over Jacket</b>	15.7 mm   0.618 in

## Representative Image



## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	400 mm   15.748 in
<b>Minimum Bend Radius, unloaded</b>	270 mm   10.63 in
<b>Tensile Load, long term, maximum</b>	6000 N   1,348.854 lbf
<b>Compression</b>	40 N/mm   228.406 lb/in
<b>Compression Test Method</b>	IEC 60794-1 E3
<b>Flex</b>	25 cycles
<b>Impact</b>	15 N-m   132.761 in lb
<b>Impact Test Method</b>	IEC 60794-1 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	IEC 60794-1 E1
<b>Twist</b>	5 cycles
<b>Twist Test Method</b>	IEC 60794-1 E7

## Optical Specifications

<b>Fiber Type</b>	G.652.D and G.657.A1, TeraSPEED®   OS2
-------------------	--

## Environmental Specifications

<b>Installation temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
---------------------------------	-------------------------------------

# 760255364 | C-096-LA-8W-M12BK/20G/GRP/D

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Cable Qualification Standards</b>	IEC 60794-1-2
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Dca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s2
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d2
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Environmental Space</b>	Aerial, lashed   Buried
<b>Flame Test Listing</b>	EN 50399
<b>Flame Test Method</b>	EN 50399
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F5

## Environmental Test Specifications

<b>Heat Age</b>	-20 °C to +85 °C (-4 °F to +185 °F)
<b>Heat Age Test Method</b>	IEC 60794-1 F9
<b>Low High Bend</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Low High Bend Test Method</b>	IEC 60794-1 E11
<b>Temperature Cycle</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1 F1

## Packaging and Weights

<b>Cable weight</b>	278 kg/km   186.807 lb/kft
---------------------	----------------------------

## Included Products

CS-8W-LT – TeraSPEED® G652D/G657A1 Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable