


# MC-KD14M-12-H10

---



Heavy Duty Double T-Arm Monopole Mount, Includes (2) Ring Mounts for 15"-50" OD Monopole, 14.5 ft x 3-1/2" OD face pipes, (12) 2-7/8" OD x 120" Antenna Pipes

Heavy Duty Double T-Arm mount design for Monopole applications featuring sturdy corner tie-backs for added stability. Includes 3-1/2" OD face pipes and (12) 2-7/8" OD Antenna Pipes.

## Product Classification

**Product Type** Monopole T-frame kit

## General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD  
**Pipe, quantity** 12  
**Sectors, quantity** 3

## Dimensions

**Height** 3,048 mm | 120 in  
**Face Width** 4.42 m | 14.5 ft  
**Width** 4,419.6 mm | 174 in  
**Pipe Length** 3,048 mm | 120 in  
**Mounting Diameter, maximum** 1270 mm | 50 in  
**Mounting Diameter, minimum** 381 mm | 15 in  
**Pipe Outer Diameter** 73.025 mm | 2.875 in  
**Stand-off Distance** 1,244.6 mm | 49 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479  
**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

# MC-KD14M-12-H10

---

**Included** Pipe mounts | Plain end pipes | Ring mounts (2) | Stand-off arms

**Packaging quantity** 1

\* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code