


1-2171012-1 | TE640P-WT02



640 Series Copper Cable, category 6A, 4 pair, UTP, CMP rated, 1000 ft reel, white

OBSOLETE

Replaced By:

UN874026804/10 CS44P ETL Verified Category 6A U/UTP Cable, plenum, white jacket, 4 pair count, 1000 ft (305 m) length reel
CS44P WHT C6A 4/23 U/UTP RL 1KFT

Product Classification

Regional Availability	Asia Australia/New Zealand Latin America
Portfolio	NETCONNECT®
Product Type	Twisted pair cable
Product Series	640 Series


General Specifications

Product Number	640P
ANSI/TIA Category	6A
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	White
Pairs, quantity	4
Transmission Standards	ANSI/TIA-568.2-D GENELEC EN 50288-6-1 ISO/IEC 11801 Class E

Dimensions

Cable Length	304.8 m 1000 ft
Diameter Over Jacket, nominal	7.239 mm 0.285 in
Conductor Gauge, singles	23 AWG

Cross Section Drawing



Electrical Specifications

Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
Safety Voltage Rating	300 V

Material Specifications

Conductor Material	Bare copper
Insulation Material	Fluoropolymer
Jacket Material	Fire retardant PVC

Environmental Specifications

Operating Temperature	-20 °C to +75 °C (-4 °F to +167 °F)
Storage Temperature	-20 °C to +75 °C (-4 °F to +167 °F)
Environmental Space	Plenum
Flame Test Method	NEC Article 800 UL 444
Smoke Test Method	CMP/FT6

Packaging and Weights

Cable weight	61.015 kg/km 41 lb/kft
Packaging Type	Reel

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

