

4

3





2

1

NOTES:

- 1.0 GENERAL NOTES
- 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS.
- 1.2 MARK PART WITH IDENTIFICATION NUMBER.
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
- 4.0 TEST
- 5.0 PACKAGING

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A	8000040218	INITIAL RELEASE	RJC	05/11/20
B	40141787CMO	REPLACE GUB-53060 WITH GUB-53050	HW1041	1/21/2022



COMMSCOPE, INC. OF NORTH CAROLINA										
TOLERANCES					SAP MATERIAL MASTER					
1 PLACE .X ± .25			3 PLACE .XXX ± 0.06		VZWSMART-MSK1					
2 PLACE .XX ± 0.12			ANGLES ± 2°							
FINISH GALV A123					MATERIAL A1011/A1018					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	CE	RJC	04/01/20	CROSSOVER PLATE, 2.375 TO 2.875 OD PIPE						
	RW	HW1041	02/15/2022							
	RV									
	AD	BCROSS	02/16/2022							
	RE	XZ1054	02/16/2022							
ECN 40141787CMO				SCALE	DOCUMENT NO.					
				1:2	VZWSMART-MSK1					
SIZE	WORK AREA	INSL	MODEL			DRAWING				SHEET
C			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	1 OF 1	
			01	RE	B	01	RE	B		

DENSITY		lbs/in ³
MASS	11.52	lbs
VOLUME	40.57	in ³
SURFACE AREA	315.68	in ²
HEIGHT	8.50"	
LENGTH	7.15"	
WIDTH	7.08"	

4

3

2

1