



Fiber OSP cable, LightScope ZWP® Blown Single Jacket All-Dielectric 2-fiber, Central Tube Construction, Singlemode G.657.A1, Gel-filled, Meters jacket marking, Black jacket color

## Product Classification

<b>Regional Availability</b>	Europe
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	B-CN


## General Specifications

<b>Cable Type</b>	Central tube, all dielectric   Microcable
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled
<b>Filler, quantity</b>	0
<b>Inner Jacket Color</b>	White
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE 810010142/DB 2x G657A1 SM [SERIAL NUMBER] [METER MARK]
<b>Subunit, quantity</b>	1
<b>Fibers per Subunit, quantity</b>	2
<b>Total Fiber Count</b>	2

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	1.9 mm   0.075 in
<b>Diameter Over Jacket</b>	2.5 mm   0.098 in

## Representative Image



## Material Specifications

**Jacket Material** Nylon

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	30 mm   1.181 in
<b>Minimum Bend Radius, storage coils</b>	30 mm   1.181 in
<b>Minimum Bend Radius, unloaded</b>	30 mm   1.181 in
<b>Tensile Load, long term, maximum</b>	75 N   16.861 lbf
<b>Compression</b>	10 N/mm   57.101 lb/in
<b>Compression Test Method</b>	IEC 60794-1-21 E3
<b>Flex</b>	25 cycles
<b>Impact</b>	2 N-m   17.701 in lb
<b>Impact Test Method</b>	IEC 60794-1-21 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	IEC 60794-1-21 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	IEC 60794-1-21 E7

## Optical Specifications

**Fiber Type** G.657.A1

## Environmental Specifications

<b>Installation temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Storage Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Cable Qualification Standards</b>	IEC 60794-1-2   IEC 60794-5-10
<b>Environmental Space</b>	Air-blown, microduct
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F5

## Environmental Test Specifications

<b>Low High Bend Test Method</b>	IEC 60794-1-21 E11
<b>Temperature Cycle</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1-22 F1

## Packaging and Weights

<b>Cable weight</b>	6.1 kg/km   4.099 lb/kft
---------------------	--------------------------

## Included Products

CS-8F-LT	-	Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber
----------	---	--

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable