

CSC1-U5A1A1BB000



NOVUX™ CSC40 Compact Fiber Closure, splice only, no adapters, no splitters, mounting tabs, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	CSC 40
Minimum Order Quantity	6

General Specifications

Cable Ports Quantity, total	2 round ports + 4 multi-out ports (8 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Pole Wall
Splicing Capacity, maximum	48
Splitter Type	No splitter
Splitter, quantity	0

Dimensions

Height	77 mm 3.031 in
---------------	------------------

CSC1-U5A1A1BB000

Width	117 mm 4.606 in
Length	215 mm 8.465 in

Environmental Specifications

Environmental Space	Outdoor
UV Resistance	UV stabilized

Packaging and Weights

Packaging quantity	1
Packaging Type	Box Carton