



OTE2 Series, Optical Terminal Enclosure, 16-port full-size connector, no splitter, gray, wall mount

- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Offers a unique solution for splicing, termination and pass-through cable applications in optical drop cable deployments
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and-play drop cable installations
- The universal cable termination system guarantees easy, fast and reliable cable fixation and manipulations

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Access terminal, without splitter/tap

Product Series

OTE

General Specifications

Application

Accepts fiber drop cables, 7 mm diameter | Accepts fiber feeder cables, 10-16 mm diameter | For holding up to 5 24-way splice trays | Offers up to 16 hardened adapter ports | Offers up to 4x4 standard cable ports

Cable Type

No cable (stubless)

Cable, quantity

0

Distribution Type

16 ports

Enclosure Color

Gray

Mounting

Handhole | Pole | Wall

Port Type

Hardened full-size SC/APC

Port, quantity

16

Splice Tray Included, quantity

4

Splice Tray Type Included

24-way, heat shrink

Splitter, quantity

1

Stub Type

No tail

Dimensions


Height

147 mm | 5.787 in


760253920 | OTE2-16IH-NN-S24-4-G

Width	372 mm 14.646 in
Depth	186 mm 7.323 in
Cable Length, stub	0 ft (0 m)

Dimension Drawing



Ordering Tree



Material Specifications

Enclosure Material Type Glass filled polypropylene (GF-PP)

760253920 | OTE2-16IH-NN-S24-4-G

Optical Specifications

Operating Wavelength Range	1260 – 1635 nm
Attenuation Terminal Connectors, maximum	0.4 dB
Insertion Loss, Terminal Connector, typical	0.16 dB
Return Loss, Connector, minimum	65 dB

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–100%, condensing
Environmental Space	Above ground Below ground Buried
Qualification Standards	IEC 60529, IP67 IEC 60529, IP68 + 1 m waterhead
UV Resistance	UV stabilized

Packaging and Weights

Included	Cable fixation kit (5) Enclosure (1) Gel Sealing kit (4) Optical splitter (1) Splice cassette (4) Wall fixation screws (4)
Packaging quantity	1
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

