


# SFG22HD-10-B

---



G22HD High Capacity Sector Frame with 2 7/8in OD x 10.5ft face. Base Kit Only. No antenna pipes.

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	High capacity Tower sector frame
<b>Product Series</b>	G2
<b>Ordering Note</b>	CommScope® standard product in the United States and Canada
<b>Warranty</b>	One year

## General Specifications

<b>Application</b>	4G LTE antenna/radio mount
<b>Mounting</b>	Angle 60°, 203.2 mm (8 in)   Straight or tapered legs up to 203.2 mm (8 in) OD
<b>Patent Number</b>	Patent pending
<b>Pipe, quantity</b>	0
<b>Sectors, quantity</b>	1
<b>Tower Taper</b>	Non-tapered   Tapered

## Dimensions

<b>Face Width</b>	3.2 m   10.5 ft
<b>Width</b>	3,200.4 mm   126 in
<b>Face Support Pipe Diameter</b>	73.025 mm   2.875 in
<b>Mounting Diameter, maximum</b>	218.44 mm   8.6 in
<b>Mounting Diameter, minimum</b>	38.1 mm   1.5 in
<b>Stand-off Distance</b>	1,041.4 mm   41 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

# SFG22HD-10-B

---

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Frame | Pipe mounts | Stiff arms (2) | Tower attachment

**Packaging quantity** 1

## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code