

SSHR-10



SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

Product Classification

Product Type	Adapter
Product Brand	SnapStak®
Ordering Note	ANDREW® standard product in the United States and Canada

General Specifications

Accessories	Adapters
Color	Black
Mounting	3/4 in through hole

Dimensions

Height	76.2 mm 3 in
Width	25.4 mm 1 in
Length	6.35 mm 0.25 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Maximum Loading	Quadruple stack for SSH-M Triple stack for hangers SSH-XL, SSH-L Triple stack, 1-5/8 in cable
Vibration Survival	≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

SSHR-10

Height, packed	17 cm 6.693 in
Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in
Packaging quantity	10
Weight, gross	0.15 kg 0.331 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

