



Fiber indoor cable, Low Smoke Zero Halogen Indoor Distribution, 2 fiber single-unit, Multimode OM4, Meters jacket marking, Aqua jacket color

## Product Classification

<b>Regional Availability</b>	China
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor cable
<b>Product Series</b>	L-DS
<b>Country Specific for</b>	China

## General Specifications

<b>Cable Type</b>	Tight buffer
<b>Jacket Color</b>	Aqua
<b>Jacket Marking</b>	Meters
<b>Strength Members</b>	E-glass yarns
<b>Total Fiber Count</b>	2

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	0.9 mm   0.035 in
<b>Diameter Over Jacket</b>	4.4 mm   0.173 in

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	88 mm   3.465 in
<b>Minimum Bend Radius, unloaded</b>	44 mm   1.732 in
<b>Tensile Load, long and short term</b>	See Sag and Tension tables in Product Documentation section
<b>Tensile Load, long term, maximum</b>	198 N   44.512 lbf
<b>Tensile Load, short term, maximum</b>	660 N   148.374 lbf
<b>Cable Crush Resistance, maximum</b>	10 N/mm   57.101 lb/in
<b>Compression</b>	10 N/mm   57.101 lb/in
<b>Compression Test Method</b>	IEC 60794-1 E3   IEC 60794-1-2 E3
<b>Strain</b>	See long and short term tensile loads

# 760255318 | L-002-DS-5X-MSUAQ/09X/B2

---

**Strain Test Method** IEC 60794-1-2-E1

## Optical Specifications

**Fiber Type** OM4

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

## Environmental Specifications

**Installation temperature** -20 °C to +60 °C (-4 °F to +140 °F)

**Operating Temperature** -20 °C to +60 °C (-4 °F to +140 °F)

**Storage Temperature** -20 °C to +60 °C (-4 °F to +140 °F)

**Cable Qualification Standards** Telcordia GR-409

**Environmental Space** Low Smoke Zero Halogen (LSZH) | Low Smoke Zero Halogen (LSZH)

**Flame Test Listing** B2

**Flame Test Method** GB/T 31247

## Environmental Test Specifications

**Temperature Cycle** -20 °C to +60 °C (-4 °F to +140 °F)

**Temperature Cycle Test Method** IEC 60794-1 F1 | IEC 60794-1-2 F1

## Included Products

CS-5X-TB-3.0/1.0/093 – OM4 Bend-Insensitive Multimode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable