CPP-DM-PANELS



CPP Distribution Module Panels

IDC

Product Classification

 Portfolio
 CommScope®

 Product Type
 RJ45 patch panel

General Specifications

Color Black

Conductor Type Solid | Stranded

Rack Type EIA 19 in

Wiring T568A | T568B

Dimensions

Termination Type

Compatible Diameter Over Dielectric, maximum1.168 mm | 0.046 inCompatible Diameter Over Dielectric, minimum0.762 mm | 0.03 inCompatible Conductor Gauge, solid22 AWG | 24 AWGCompatible Conductor Gauge, stranded22 AWG | 24 AWG

Electrical Specifications

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 mOhm

Material Specifications

Contact Plating Material Precious metals

Material Type High-impact, flame retardant, thermoplastic | Powder-

coated steel

Termination Contact Plating Nickel

COMMSCOPE®

CPP-DM-PANELS

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Insertion Life, test plug IEC 60603-7 compliant plug

Plug Retention Force, minimum 133 N | 29.9 lbf

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative HumidityUp to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard UL | cUL