# MPT-A2D-BB-NN-500M



HELIAX® Power cable, with aluminum shield with quantity, 2x25 mm2 cores, flame resistant CPR Class B2ca s1, d2, a1 rated, 500 meters

Available with different colors on demand

#### Product Classification

Regional Availability	Europe
Portfolio	CommScope®
Product Type	Power cable
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product
Warranty	For more information, please consult our Product Warranty guidelines

### General Specifications

Application	Remote radio head
Cable Type	Power
Conductor Type, singles	Stranded
Conductors, quantity	2
Jacket Color	Black
Jacket Color, singles	Blue   Brown
Dimensions	
Cable Length	500.024 m   1,640.5 ft
Diameter Over Jacket	15.977 mm   0.629 in

25 mm<sup>2</sup>

## Cross Section Drawing


**Conductor Gauge** 

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 16, 2024



# MPT-A2D-BB-NN-500M




#### Electrical Specifications

Safety Voltage Rating

600 V

# Ordering Tree



Notes

this size is not available for 6, 8, or 12 core cable options.

\*\* this size is not available for 8 and 12 core cable options.

# Material Specifications

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 16, 2024

**COMMSCOPE**°

# MPT-A2D-BB-NN-500M

Conductor Material	Tinned copper
Ground Wire Material	Annealed aluminum wires
Insulation Material, singles	Flame retardant PE
Jacket Material	Flame retardant PE
Outer Shield (Braid) Coverage	100 %
Outer Shield (Tape) Material	AI/PET tape

## **Environmental Specifications**

Installation temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-40 °C to +90 °C (-40 °F to +194 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Environmental Space	Indoor/Outdoor
Jacket UV Resistance	UV stabilized

## Packaging and Weights

Cable weight
--------------

579.027 kg/km | 389.088 lb/kft

### \* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
Operating Temperature	Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 16, 2024

