

8-port multibeam antenna, 8x 1695-2690 MHz, 33° HPBW, 4xRET

- Enhances network capacity and spectrum utilization when used in six sector applications
- Reduces antenna count to minimize Cap-Ex and Op-Ex costs 3 antennas required for 6 sector configurations

General Specifications

Antenna Type Multibeam

Band Single band

Color Light Gray (RAL 7035)

Grounding TypeRF connector inner conductor and body grounded to reflector and mounting

bracket

Performance Note Outdoor usage

Radome Material Fiberglass, UV resistant

 Radiator Material
 Aluminum

 Reflector Material
 Aluminum

 RF Connector Interface
 4 3-10 Female

RF Connector Location Bottom

RF Connector Quantity, mid band 8
RF Connector Quantity, total 8

Remote Electrical Tilt (RET) Information

RET Hardware CommRET v2

RET Interface 8-pin DIN Female | 8-pin DIN Male

RET Interface, quantity 1 female | 1 male

 Input Voltage
 10-30 Vdc

 Internal RET
 Mid band (4)

Power Consumption, active state, maximum 10 W Power Consumption, idle state, maximum 2 W

Protocol 3GPP/AISG 2.0 (Single RET)

Dimensions

Width 397 mm | 15.63 in

Page 1 of 5




Depth 197 mm | 7.756 in

Length 1997 mm | 78.622 in

Net Weight, antenna only 21.2 kg | 46.738 lb


Array Layout



Array ID	Frequency (MHz)	RF Connector	HPBW	RET (SRET)	AISG No.	AISG RET UID	
Y1	1695-2690	1 - 2	33°	1	AISG1	CPxxxxxxxxxxxxxY1	
Y2	1695-2690	3 - 4	33°	2	AISG1	CPxxxxxxxxxxxxxY2	
Y3	1695-2690	5 - 6	33°	3	AISG1	CPxxxxxxxxxxxxxXY3	
Y4	1695-2690	7 - 8	33°	4	AISG1	CPxxxxxxxxxxxxx4	

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1695 – 2690 MHz

Polarization ±45°

Total Input Power, maximum 1,000 W

BASTA Version, electricalBASTA v11

Electrical Specifications

	Y1-Y4	Y1-Y4	Y1-Y4	Y1-Y4
Frequency Band, MHz	1695-1995	1920-2300	2300-2500	2490-2690
RF Port	1-8	1-8	1-8	1-8
Gain, dBi	18.3	19.1	19.8	19.8
Beam Centers, Horizontal, degrees	±30	±30	±30	±30
Beamwidth, Horizontal, degrees	39	35	30	28
Beamwidth, Vertical, degrees	9.8	8.8	7.5	6.9
Beam Tilt, degrees	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	16	21	21	20
Front-to-Back Ratio, Copolarization 180° ± 30°, dB	29	31	30	29
Isolation, Cross Polarization, dB	25	25	25	25
Isolation, Inter-band, dB	26	26	26	26
Isolation, Beam to Beam, dB	26	26	26	26
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150
Input Power per Port, maximum, watts	200	200	200	200

Electrical Specifications, BASTA

Frequency Band, MHz	1695-1995	1920-2300	2300-2500	2490-2690
Gain by all Beam Tilts, average, dBi	17.6	18.5	19.4	19.5
Gain by all Beam Tilts Tolerance, dB	±0.9	±0.7	±0.6	±0.4
Beamwidth, Horizontal Tolerance, degrees	±2	±3	±1	±1
Beamwidth, Vertical Tolerance, degrees	±0.7	±0.7	±0.6	±0.4
CPR at Boresight, dB	20	23	26	23

Page 3 of 5



Mechanical Specifications

 Wind Loading @ Velocity, frontal
 625.0 N @ 150 km/h (140.5 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 289.0 N @ 150 km/h (65.0 lbf @ 150 km/h)

Wind Loading @ Velocity, rear 270.0 N @ 150 km/h (60.7 lbf @ 150 km/h)

Wind Speed, maximum 200 km/h (124 mph)

Packaging and Weights

 Width, packed
 492 mm | 19.37 in

 Depth, packed
 317 mm | 12.48 in

 Length, packed
 2197 mm | 86.496 in

 Weight, gross
 32 kg | 70.548 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

UK-ROHS Compliant

Included Products

BSAMNT-B95-04 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.


Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



BSAMNT-B95-04



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net4.5 kg | 9.921 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 2

Regulatory Compliance/Certifications

Agency Classification

CE Compliant with the relevant CE product directives

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

 ϵ

