



Fiber OSP cable, LightScope ZWP® Mini Single Jacket All-Dielectric, Singlemode G.657.A1, 12 fiber Arid Core construction, Gel-filled, stranded loose tube, Meters jacket marking, Black jacket color

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	O-LN

## General Specifications

<b>Cable Type</b>	Stranded loose tube
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled
<b>Filler, quantity</b>	5
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE G657A1 SM 48 FIBER (SERIAL NUMBER) (MM/YYYY) (METER MARK)
<b>Subunit, quantity</b>	1
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	12

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	2 mm   0.079 in
<b>Diameter Over Jacket</b>	9.5 mm   0.374 in

## Representative Image



## Material Specifications

**Jacket Material** PE

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	143 mm   5.63 in
<b>Minimum Bend Radius, unloaded</b>	95 mm   3.74 in
<b>Tensile Load, long term, maximum</b>	800 N   179.847 lbf
<b>Tensile Load, short term, maximum</b>	2700 N   606.984 lbf
<b>Compression</b>	22 N/mm   125.623 lb/in
<b>Compression Test Method</b>	IEC 60794-1 E3
<b>Flex</b>	25 cycles
<b>Flex Test Method</b>	IEC 60794-1 E6
<b>Impact</b>	2.94 N-m   26.021 in lb
<b>Impact Test Method</b>	IEC 60794-1 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	IEC 60794-1 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	IEC 60794-1 E7
<b>Vertical Rise, maximum</b>	1142 m   3,746.719 ft

## Optical Specifications

**Fiber Type** G.657.A1

## Environmental Specifications

# 810010365/DB | O-012-LN-8F-M12NS/20G/BK

<b>Installation temperature</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Cable Qualification Standards</b>	ANSI/ICEA S-87-640   EN 187105   IEC 60794-1-2
<b>Environmental Space</b>	Aerial, lashed   Buried
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F5

## Environmental Test Specifications

<b>Cable Freeze</b>	-2 °C   28.4 °F
<b>Cable Freeze Test Method</b>	IEC 60794-1 F15
<b>Drip</b>	70 °C   158 °F
<b>Drip Test Method</b>	IEC 60794-1 E14
<b>Heat Age</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Heat Age Test Method</b>	IEC 60794-1 F9
<b>Low High Bend</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Low High Bend Test Method</b>	IEC 60794-1 E11
<b>Temperature Cycle</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1 F1

## Packaging and Weights

<b>Cable weight</b>	72 kg/km   48.382 lb/kft
---------------------	--------------------------

## Included Products

CS-8F-TB	- Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber
----------	--

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable