

# FIST-PANELS

---



## FIST Fiber Termination and/or Splice Panels

The FIST Fiber Optic Panels are offered in 4 families:

### FIST-GMS2

The FIST-GMS2 features the FIST fiber management system and is a multi-purpose mechanical shelf assembly used to store splices of external/ indoor cable to pigtails. These shelves combine splice, storage and patching functions. The shelf accommodates a patch panel containing 24 standard or 48 small-form factor connections.

### FIST-GSS2/GSS3

The FIST-GSS2 and FIST-GSS3 multi-purpose splice shelves feature FIST fiber management system technology. They mount in ETSI (FIST-GR3), 19- or 15-inch (FIST-GR3F) racks.

### FIST-GPS2/GPS3

FIST-GPS shelves feature the FIST fiber management system and provide a platform for patching and splicing within a rack environment. The shelves house FIST splice and patch trays (FIST-GPST-12 or FIST-GPSTF-12). They mount in ETSI (FIST-GR3), 19- or 15-inch (FIST-GR3F) racks.

### OCSH

The OCSH is a mechanical shelf assembly that accommodates OCM6 splitter or xWDM modules in a rack or cabinet environment. The shelf is typically used in 15-inch, ETSI or 19-inch active racks or data racks, and is also compatible with CommScope racks and cabinets using the FIST fiber management system.

### Main features:

- Easy identification of each fiber
- Various connector/adaptor types possible
- Available with various capacities and in different heights

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber VAM panel   Fiber patch panel   Fiber patch/splice panel   Fiber splice panel
<b>Product Brand</b>	FIST®
<b>Product Series</b>	FIST-GMS2   FIST-GPS2   FIST-GPS3   FIST-GSS2   FIST-GSS3   OCSH

## General Specifications

<b>Functionality</b>	Multiplexing   Patching   Splicing   Splitting
----------------------	--

# FIST-PANELS

---

**Interface, front** LC/APC | LC/UPC | SC/APC | SC/UPC | Unloaded

**Rack Type** EIA 19 in | ETSI 600 mm

**Shelf Movement** Sliding

## Material Specifications

**Finish** Powder coated

**Material Type** Galvanized steel

## Environmental Specifications

**Operating Temperature** -5 °C to +45 °C (+23 °F to +113 °F)

**Storage Temperature** -30 °C to +60 °C (-22 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

## Packaging and Weights

**Included** Mounting hardware